

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	31OCT2016	JY	SH
	B	ADD NEW PN 4-2170808-7	21MAY2019	JY	SH

HEAT SINK CLIP

HEAT SINK

LIGHT PIPE

1x2 CAGE ASSEMBLY

2-2170808-1 AS SHOWN
SCALE 2:1

1. COMPONENTS
CAGE ASSEMBLY: NICKEL-SILVER ALLOY
HEAT SINK: ALUMINUM/BLACK ANODIZE
HEAT SINK CLIP: STAINLESS STEEL
EMI SPRING: COPPER ALLOY/NICKEL PLATE
LIGHT PIPE: CLEAR POLYCARBONATE

2. REFERENCE APPLICATION SPECIFICATION 114-32023
FOR RECOMMENDED DRILL HOLE DIAMETER AND
PLATING THICKNESS


3. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER


4. DIMENSION APPLIES WITH MODULE INSERTED IN CAGE

5. HEAT SINKS, HEAT SINK CLIPS AND LIGHT PIPES
ARE SHIPPED ASSEMBLED ON CAGE

6. MINIMUM PC BOARD THICKNESS: SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 2.20 MIN


7. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
8. THESE HOLES ARE OPTIONAL WHEN THE REAR PINS ARE REMOVED.
9. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.
10. DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.
11. NOTED DIMENSIONS ONLY APPLY TO CAGE ASSEMBLY WITH LIGHT PIPE.
12. PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 16SEP2014	 TE Connectivity		
DIMENSIONS: mm		CHK JASON YANG 16SEP2014			
		APVD -	NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES		
		PRODUCT SPEC 108-19428	SIZE A200779		
MATERIAL SEE NOTES		APPLICATION SPEC 114-32023	CAGE CODE C-2170808		RESTRICTED TO -
FINISH SEE NOTES		WEIGHT -	DRAWING NO C-2170808		REV B
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 9	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


HEAT SINK OPTION



PCI HEAT SINK HEIGHT
SCALE 1:1




SAN HEAT SINK HEIGHT
SCALE 1:1




NETWORKING HEAT SINK HEIGHT
SCALE 1:1


LIGHT PIPE OPTION



SINGLE LIGHT PIPE
SCALE 1:1




DUAL LIGHT PIPE
SCALE 1:1




QUAD LIGHT PIPE
SCALE 1:1

OF REAR PIN OPTION



1 REAR PIN
SCALE 3:1



0 REAR PIN
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU CHK JASON YANG APVD -	16SEP2014 16SEP2014 -	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.25 2 PLC ±0.2 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES	
MATERIAL SEE NOTES		PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023 WEIGHT -		SIZE A200779	CAGE CODE C-2170808
		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 9
				REV B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0	3.4	16.0	SAN	COATED QUAD LP	5-2170808-5
1	2.9	18.4	CUSTOMIZED	QUAD LP	4-2170808-7
0	2.9	23.0	NETWORKING	QUAD LP	4-2170808-6
0	2.9	16.0	SAN	QUAD LP	4-2170808-5
0	2.9	13.7	PCI	QUAD LP	4-2170808-4
1	2.9	23.0	NETWORKING	QUAD LP	4-2170808-3
1	2.9	16.0	SAN	QUAD LP	4-2170808-2
1	2.9	13.7	PCI	QUAD LP	4-2170808-1
1	4.5	13.7	PCI	SHORTER, QUAD LP	4-2170808-0
0	2.9	23.0	NETWORKING	DUAL LP	2-2170808-6
0	2.9	16.0	SAN	DUAL LP	2-2170808-5
0	2.9	13.7	PCI	DUAL LP	2-2170808-4
1	2.9	23.0	NETWORKING	DUAL LP	2-2170808-3
1	2.9	16.0	SAN	DUAL LP	2-2170808-2
1	2.9	13.7	PCI	DUAL LP	2-2170808-1
0	2.9	23.0	NETWORKING	SINGLE LP	2170808-6
0	2.9	16.0	SAN	SINGLE LP	2170808-5
0	2.9	13.7	PCI	SINGLE LP	2170808-4
1	2.9	23.0	NETWORKING	SINGLE LP	2170808-3
1	2.9	16.0	SAN	SINGLE LP	2170808-2
1	2.9	13.7	PCI	SINGLE LP	2170808-1
# OF REAR PIN	DIM B (LP EXTRUDE)	DIM A (PRODUCT HEIGHT)	APPLICATION	LIGHT PIPE OPTION	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC ±
1 PLC ±0.25
2 PLC ±0.2
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

DWN
BING LIU
CHK
JASON YANG
APVD
-
PRODUCT SPEC
108-19428
APPLICATION SPEC
114-32023
WEIGHT
-
CUSTOMER DRAWING

16SEP2014
16SEP2014

-

NAME
RECEPTACLE CAGE ASSEMBLY
1X2, QSFP28, THRU BEZEL, SPRING
WITH HEAT SINKS AND LIGHT PIPES

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2170808

RESTRICTED TO
-


SCALE
1:1

SHEET
3 OF 9

REV
B


1471-9 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



CAGE ASSEMBLY IS OMITED

SINGLE SIDE MOUNTING
SCALE 2:1



CAGE ASSEMBLY IS OMITED

SINGLE SIDE MOUNTING
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.25

2 PLC ±0.2

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

SEE NOTES

-

DWN BING LIU 16SEP2014

CHK JASON YANG 16SEP2014

APVD -

PRODUCT SPEC 108-19428

APPLICATION SPEC 114-32023

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2170808

-

-

SCALE 1:1

SHEET 4 OF 9

REV B

D

C

B


A

D


C

B


A




CAGE ASSEMBLY IS OMITED



CAGE ASSEMBLY IS OMITED



BELLY TO BELLY MOUNTING
SCALE 2:1





BELLY TO BELLY MOUNTING
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 16SEP2014	 TE Connectivity			
		CHK JASON YANG 16SEP2014				
DIMENSIONS: mm		APVD -	NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES			
		PRODUCT SPEC 108-19428				
0 PLC ± 1 PLC ±0.25 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC 114-32023	SIZE A2		CAGE CODE 00779	
MATERIAL SEE NOTES -		WEIGHT -	DRAWING NO C-2170808		RESTRICTED TO -	
FINISH SEE NOTES -		CUSTOMER DRAWING		SCALE 1:1	SHEET 5 OF 9	REV B



1471-9 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 16SEP2014 CHK JASON YANG 16SEP2014 APVD -		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.25 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± MATERIAL SEE NOTES FINISH SEE NOTES		NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES	
		PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023 WEIGHT -		SIZE A2	CAGE CODE 00779
				DRAWING NO C-2170808	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 1:1	SHEET 7 OF 9
				REV	B

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 16SEP2014		 TE Connectivity	
		CHR JASON YANG 16SEP2014			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES	
		APVD -			
		PRODUCT SPEC 108-19428			
		APPLICATION SPEC 114-32023			
MATERIAL SEE NOTES -		FINISH SEE NOTES -		SIZE A2	CAGE CODE 00779
		WEIGHT -		DRAWING NO C-2170808	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 1:1	SHEET 8 of 9
				REV R	



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

BING LIU

16SEP2014

CHK

JASON YANG

16SEP2014

APVD

-

-

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.25

2 PLC ±0.2

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

MATERIAL

SEE NOTES

-

PRODUCT SPEC

108-19428

APPLICATION SPEC

114-32023

WEIGHT

-

CUSTOMER DRAWING

SCALE 1:1

SHEET 9 OF 9

REV B

TE Connectivity

NAME

RECEPTACLE CAGE ASSEMBLY

1X2, QSFP28, THRU BEZEL, SPRING

WITH HEAT SINKS AND LIGHT PIPES

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-2170808

RESTRICTED TO

-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170808-5](#)