



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRODUCTION ISSUE	06JUL2017	NN	AP



Dimensions in mm [inches for reference]

Part No.	To Fit Connector Size	H		J		K		P REF b	R REF b	U		W ±20% b	X ±20% b
		MIN a	±5% b	MIN a	±5% b	MIN a	MAX b			MIN a	±20% b		
214A011-25C-0	9 WAY	20.8 [.82]	20.3 [.80]	15.7 [.62]	10.7 [.42]	9.0 [.35]	4.1 [.16]	33.0 [1.30]	19.0 [.75]	2.0 [.08]	4.0 [.16]	1.0 [.04]	3.0 [.12]
214A021-25C-0	15 WAY	29.0 [1.14]	28.2 [1.11]	15.7 [.62]	10.7 [.42]	11.0 [.43]	5.3 [.21]	39.0 [1.54]	22.0 [.87]	3.8 [.15]	6.0 [.24]	1.0 [.04]	3.0 [.12]
214A032-25C-0	25 WAY	42.8 [1.69]	42.2 [1.66]	15.7 [.62]	10.7 [.42]	15.0 [.59]	8.1 [.32]	45.0 [1.77]	25.0 [.98]	5.0 [.20]	6.3 [.25]	1.0 [.04]	3.0 [.12]
214A042-25C-0	37 WAY	59.5 [2.34]	58.7 [2.31]	15.0 [.59]	10.7 [.42]	19.0 [.75]	8.6 [.34]	53.0 [2.09]	28.0 [1.10]	5.0 [.20]	9.0 [.35]	1.0 [.04]	3.0 [.12]
214A052-25C-0	50 WAY	58.0 [2.28]	57.9 [2.28]	17.5 [.69]	13.7 [.54]	21.0 [.83]	10.7 [.42]	61.0 [2.40]	32.0 [1.26]	6.5 [.26]	10.0 [.39]	1.0 [.04]	3.0 [.12]

DIMENSIONS:

mm [INCHES]

DWN

N. NAGAR

06JUL2017

CHK

—

APVD

A. POOLE

06JUL2017

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

CUSTOMER DRAWING

MATERIAL

—

FINISH

—



TE Connectivity

NAME

RECTANGULAR BOOT SUBMINITURE STRAIGHT, COATED
214A0XX-25C-0

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-214A0XX-25C-0

RESTRICTED TO

—

SCALE

DNS

SHEET

1 OF 2

REV

1


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 By TE Connectivity

0 PLC ± —
 1 PLC ± —
 2 PLC ± —
 3 PLC ± —
 4 PLC ± —
 ANGLES ± —



REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash No.	Material Description	SPEC No.	Coating Slash No.
-25C	ELASTOMER/SILVER COMPOSITE	RW-3047	/86, /200

ORDERING INFORMATION

214A0**-25C/**-0



Adhesive Slash Number

Material Dash Number (see compatibility chart)

Base Part Number

NOTES



- As supplied dimensions are for parts without adhesive, when an adhesive layer is added entry diameters will reduce by 1.5mm Max.

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2017 By TE Connectivity

DIMENSIONS: mm [INCHES]		DWN N. NAGAR 06JUL2017	MATERIAL —		FINISH —	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK —	 TE Connectivity			
		APVD A. POOLE 06JUL2017				
		PRODUCT SPEC —	NAME RECTANGULAR BOOT SUBMINITURE STRAIGHT, COATED 214A0XX-25C-0			
		APPLICATION SPEC —				
		WEIGHT	SIZE A4	CAGE CODE 00779	DRAWING NO C-214A0XX-25C-0	RESTRICTED TO —
		CUSTOMER DRAWING			SCALE DNS	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EM3623-000](#)