

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

12JUN2012

© COPYRIGHT 2012

BY Tyco Electronics Japan G.K.


ALL RIGHTS RESERVED.

LOC
JDIST
-


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	06DEC2013	T.S	N.Y
	B	ADD ITEM	18NOV2014	T.S	N.Y
	C	RELEASED PER ECR-18-015311	26SEP2018	PP	RB



- I. -1 : TYPE I , INSULATION DIAMETER 1.05-1.15mm
I- -1 : TYPE II, INSULATION DIAMETER 1.05-1.15mm
-2 : TYPE I , INSULATION DIAMETER 0.93-1.05mm
I- -2 : TYPE II, INSULATION DIAMETER 0.93-1.05mm
-3 : TYPE I , INSULATION DIAMETER 0.93-1.05mm IPC, 1.05-1.15mm IPC
-6 : TYPE I , INSULATION DIAMETER 1.1-1.2mm







MATING SHAPE : TYPE I
2201855-1/-2/-3/-6
SCALE 3:1



MATING SHAPE : TYPE II
1-2201855-1/-2
SCALE 3:1



CIRCUIT NO.



-1 : AS SHONW

1	1	1	1	1	1	THERMO PLASTIC	PLUG COVER HSG BOTTOM	7
1	1	1	1	1	1	THERMO PLASTIC	LOCK HSG	6
2	-	-	-	-	-	THERMO PLASTIC	CABLE HSG Ø1.10-1.20 COLOR : GREEN	5
-	1	2	2	-	-		CABLE HSG Ø0.93-1.05 COLOR : RED	
-	1	-	-	2	2		CABLE HSG Ø1.05-1.15 COLOR : BLUE	
1	1	1	1	1	1	HSG MATERIAL:THERMO PLASTIC CONTACT MATERIAL:COPPER ALLOY FINISH:NI PLATING ALL OVER CONTACT AREA Au PLATING TERMINATION AREA Au PLATING	PLUG SUB ASSY	4
1	1	1	1	1	1	MATERIAL:COPPER ALLOY FINISH:NICKEL PLATING	BOTTOM SHELL	3
-	-	1	-	1	-	MATERIAL:COPPER ALLOY FINISH:NICKEL PLATING	PLUG TOP SHELL TYPEII	2
1	1	-	1	-	1	MATERIAL:COPPER ALLOY FINISH:NICKEL PLATING	PLUG TOP SHELL TYPEI	
1	1	1	1	1	1	THERMO PLASTIC	PLUG COVER HSG TOP	1
-6	-3	1- -2	-2	1- -1	-1	MATERIAL/FINISH	PART NAME	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 06DEC2013

T.SHIMOYASU

CHK 06DEC2013

M.HARASAWA

APVD 06DEC2013

N.YAMASAKI

PRODUCT SPEC

108-78955

APPLICATION SPEC

114-5506

WEIGHT -

CUSTOMER DRAWING

TE

TE Connectivity

NAME INDUSTRIAL MINI I/O PIERCING PLUG CONNECTOR KIT			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2201855	
SCALE 2:1		SHEET 1 OF 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2201855-3](#)