

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT20

BY -

ALL RIGHTS RESERVED.

NOTES:

1 ASSEMBLIES TO BE TESTED FOR 100% CONTINUITY

2 ASSEMBLIES ARE PACKAGED ACCORDING PACKAGING SPEC 107-19582

3 RED MARKED CORRESPONDS TO PIN 1

4 FOR MOW TO PB SEE 2205068

SCALE : 4:1

0.25 MAX

“ L ”

0.25 MAX

SIDE A

2205060-X (4 POSITION CABLE ASSEMBLY) AS SHOWN

SIDE B

0.25 MAX

“ L ”

0.25 MAX

SIDE A

2205060-X (4 POSITION CABLE ASSEMBLY) AS SHOWN

SIDE B

2205076-3

20

200

CA MICRO-MATCH MOW -MOW

20POS

2205076-2

20

150

CA MICRO-MATCH MOW -MOW

20POS

2205076-1

20

75

CA MICRO-MATCH MOW -MOW

20POS

2205067-3

18

200

CA MICRO-MATCH MOW -MOW

18POS

2205067-2

18

150

CA MICRO-MATCH MOW -MOW

18POS

2205067-1

18

75

CA MICRO-MATCH MOW -MOW

18POS

2205066-3

16

200

CA MICRO-MATCH MOW -MOW

16POS

2205066-2

16

150

CA MICRO-MATCH MOW -MOW

16POS

2205066-1

16

75

CA MICRO-MATCH MOW -MOW

16POS

2205065-3

14

200

CA MICRO-MATCH MOW -MOW

14POS

2205065-2

14

150

CA MICRO-MATCH MOW -MOW

14POS

2205065-1

14

75

CA MICRO-MATCH MOW -MOW

14POS

2205064-3

12

200

CA MICRO-MATCH MOW -MOW

12POS

2205064-2

12

150

CA MICRO-MATCH MOW -MOW

12POS

2205064-1

12

75

CA MICRO-MATCH MOW -MOW

12POS

2205063-3

10

200

CA MICRO-MATCH MOW -MOW

10POS

2205063-2

10

150

CA MICRO-MATCH MOW -MOW

10POS

2205063-1

10

75

CA MICRO-MATCH MOW -MOW

10POS

2205062-3

8

200

CA MICRO-MATCH MOW -MOW

8POS

2205062-2

8

150

CA MICRO-MATCH MOW -MOW

8POS

2205062-1

8

75

CA MICRO-MATCH MOW -MOW

8POS

2205061-3

6

200

CA MICRO-MATCH MOW -MOW

6POS

2205061-2

6

150

CA MICRO-MATCH MOW -MOW

6POS

2205061-1

6

75

CA MICRO-MATCH MOW -MOW

6POS

2205060-3

4

200

CA MICRO-MATCH MOW -MOW

4POS

2205060-2

4

150

CA MICRO-MATCH MOW -MOW

4POS

2205060-1

4

75

CA MICRO-MATCH MOW -MOW

4POS

TE PN

POS

LENGTH

DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 13DEC2013
RAGHAVENDRA K

CHK 23DEC2013
B. VELDHOVEN

APVD 23DEC2013
G. DOREMALEN VAN

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

MATERIAL

-

-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

Customer Drawing

TE Connectivity

CABLE ASSY MICRO-MATCH MOW -MOW

SIZE A2

CAGE CODE -

DRAWING NO. ©2205060

RESTRICTED TO -

SCALE 5:1

SHEET 1 OF 1

REV B

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2205064-1](#)