






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	10SEP2016	RS	ML
	A1	REVISED PER ECR-16-016988	04JAN2017	RK	PO



1. HOUSING MATERIAL: THERMOPLASTIC, FLAME-RETARDANT PER UL 94 V-0
COLOR = BLACK
2. CONTACT MATERIAL: COPPER ALLOY WITH STEEL WIRE CLAMP
3. RETENTION CLIP LOCATED ADJACENT TO BOTTOM SURFACE AS SHOWN.
4. WIRE SIZE: 26-12 AWG
5. SCREW TIGHTENING TORQUE: 0.5 N·m
6. PRODUCT CERTIFICATIONS:
UL, CSA: 300V (SEE TABLE FOR RATED CURRENT)
7. HAZARDOUS SUBSTANCE COMPLIANCE: RoHS, REACH
8. MATES WITH 2305908 SERIES



10A (GROUP D&E)	60.0	12	1-2213934-2
	55.0	11	1-2213934-1
	50.0	10	1-2213934-0
15A (GROUP B)	45.0	9	2213934-9
	40.0	8	2213934-8
	35.0	7	2213934-7
	30.0	6	2213934-6
	25.0	5	2213934-5
	20.0	4	2213934-4
	15.0	3	2213934-3
	10.0	2	2213934-2
RATED CURRENT	LENGTH "L" (mm)	NO. OF POLES	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10SEP2016 RAVL.S		 TE Connectivity				
DIMENSIONS: mm		CHK 10SEP2016 LUKSIC MAREK						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 10SEP2016 LUKSIC MAREK		NAME SOCKET TERMINAL BLOCK, PERPENDICULAR, 5.0MM PITCH, BOTTOM RETENTION				
		PRODUCT SPEC						
		-						
		APPLICATION SPEC						
		-						
MATERIAL SEE NOTES		WEIGHT -		SIZE A2	CAGE CODE -	DRAWING NO C=2213934	RESTRICTED TO -	
FINISH -		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 2	REV A1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

COPYRIGHT copyright.d8Ye-

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

2 POLES: 2213934-2

3 POLES: 2213934-3

4 POLES: 2213934-4

5 POLES: 2213934-5

6 POLES: 2213934-6

7 POLES: 2213934-7

8 POLES: 2213934-8

9 POLES: 2213934-9

10 POLES: 1-2213934-0

11 POLES: 1-2213934-1

12 POLES: 1-2213934-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWNRAVL.S10SEP2016

CHKLUKSIC MAREK10SEP2016

APVDLUKSIC MAREK10SEP2016

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC±0.2

1 PLC±0.13

2 PLC±0.13

3 PLC±0.13

4 PLC±0.13

ANGLES±

FINISH-

MATERIAL

-

-

DWNRAVL.S10SEP2016

CHKLUKSIC MAREK10SEP2016

APVDLUKSIC MAREK10SEP2016

PRODUCT SPEC-

APPLICATION SPEC-

WEIGHT-

CUSTOMER DRAWING

TE

TE Connectivity

NAME

SOCKET TERMINAL BLOCK, PERPENDICULAR, 5.0MM PITCH, BOTTOM RETENTION

SIZEA2

CAGE CODE-

DRAWING NO.C-2213934

RESTRICTED TO-

SCALE5:1

SHEET2 OF 2

REVA1

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2213934-2](#)