


4		3		2		1							
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS					
© COPYRIGHT – By –		ALL RIGHTS RESERVED.		H		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
NOTES: Tolerances cable lengths: 0m to 0.5m +30mm 0.5m to 1.0m +50mm 1.0m to 3.0m +100mm < 3.0m +1.5%									A	INITIAL RELEASE	12NOV2013	GSK	BvH
									A1	ECR-14-011671	14AUG2014	GSK	BvH
TECHNICAL DATA													
Operating voltage		max. 60 V AC/DC											
Operating current per contact		max. 4 A											
Locking of ports		Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing											
Protection		IP65 and IP67 when plugged and screwed down (EN 60529)											
PUR CABLE													
No./diameter of wires		3 x 0.34 mm²											
Wire isolation		PP (br, bl, bk)											
C-track properties		5 million											
Jacket		PUR (UL/CSA)											
Outer diameter		approx. 5.0 mm											
Bend radius (moving)		10 x outer diameter											
Temperature range (fixed)		-40...+80 °C											
Temperature range (mobile)		-25...+80 °C											
PVC CABLE													
No./diameter of wires		3 X 0.34 mm²											
Wire isolation		PVC (br, bl, bk)											
C-track properties													
Jacket		PVC (UL/CSA)											
Outer diameter		approx. 5.0 mm											
Bend radius (moving)		10 x outer diameter											
Temperature range (fixed)		-30...+80 °C											
Temperature range (mobile)		-5...+80 °C											
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:											
mm													
		0 PLC ± -											
		1 PLC ± -											
		2 PLC ± -											
		3 PLC ± -											
		4 PLC ± -											
		ANGLES ± -											
MATERIAL		FINISH											
-		-											
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 12NOV2013 SATHISH KUMAR .G		 TE Connectivity							
				CHK 12NOV2013 B.VELDHOVEN									
				APVD 12NOV2013 A.VAN ZANDVOORT									
				PRODUCT SPEC		NAME							
				108-19483		M8 X 1.0 STRAIGHT SOCKET PIGTAIL SHLD							
				APPLICATION SPEC									
				114-32127									
				WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
				-		A3		00779		C-2273005		-	
CUSTOMER DRAWING				SCALE		SHEET		REV					
				NTS		1 OF 1		A1					

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2273005-2](#)