

REVISIONS		DATE	BY	APP'D
NO.	DESCRIPTION	17/02/2014	GF	SM
P	LTR			
A	FIRST VERSION			

NOTES :

△ MATERIALS AND FINISH:

- HOUSING: PA66
- CONTACTS: COPPER ALLOY, FINISH: TIN OVER NICKEL UNDERPLATE
- SPRING: STAINLESS STRIP STEEL

2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)

3. WIRE TYPES AND SIZES ACCEPTED
WIRE RANGE: 20AWG~26AWG.
STRIP LENGTH: 9.5mm~10.5mm

4. PACKAGED IN TRAY.

5. CURRENT RATING: 6amp AC150V.

6. OPERATION TEMPERATURE: -40°C TO +105°C

P/N: *-2834015-*

COLOR CODE:





PIN No:

SERIES CODE

- | | |
|----------|----------|
| 1=GREEN | 2=2 POSN |
| 2=BLUE | 3=3 POSN |
| 3=BROWN | 4=4 POSN |
| 4=ORANGE | 5=5 POSN |
| 5=GREY | 6=6 POSN |
| 6=RED | 7=7 POSN |
| 7=YELLOW | 8=8 POSN |
| 8=PURPLE | |
| 9=WHITE | |
| 0=BLACK | |

REMARK: THE DIFFERENT COLORS COULD BE COMBINED
TO THE NEW CONNECTOR P/Ns FOR CUSTOMER REQUEST.

PCB Layout



DETAIL INNER

23.32	8 POSN
20.78	7 POSN
18.24	6 POSN
15.70	5 POSN
13.16	4 POSN
10.62	3 POSN
8.08	2 POSN
A	NO. OF POSITIONS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE: 14JAN2015		DRAWN BY: SHI MING	
DRAWING NO: 1008-137079		DATE: 14JAN2015		CHECKED BY: SHI MING	
REVISION: 1		DATE: 14JAN2015		DRAWN BY: SHI MING	
APPLICATION: 114-137079		DATE: 14JAN2015		CHECKED BY: SHI MING	
VERSION: 1		DATE: 14JAN2015		DRAWN BY: SHI MING	
CUSTOMER DRAWING		DATE: 14JAN2015		DRAWN BY: SHI MING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2834015-3](#)