

316081

NUMBER



3rd ANGLE PROJECTION

METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

VIEW A

回路番号
CIRCUIT NOAMPマーク
シリーズマーク
SERIES MARKタブコンタクト
TAB CONTACTリテンションレグ
RETENTION LEGコンタクト半田付部
CONTACT TAIL

X-X KEY

NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 0.76 μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注記

- 材料: ハウジング: ガラス入り熱可塑性
ポリエスチル樹脂 (94V-0), 色: 黒
コンタクト: 銅合金
リテンションレグ: 銅合金
- めっき: コンタクト: 全面Ni下地
接触部: 0.38 μm MIN金めっき
- めっき: コンタクト: 全面Ni下地
接触部: 0.76 μm MIN金めっき
- めっき: コンタクト: 全面Ni下地
接触部: 2.0 μm MINスズめっき
- めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上に半田めっき
- めっき: リテンションレグとコンタクト半田付部: ニッケル下地の上にスズめっき

B4	REVISED PER ECO-11-005030	RK	HMR	20MAR 11
LTR	REVISION RECORD	DR	CHK	DATE

DR.	4/JUL/95	DE.	4/JUL/95
K.IKEDA		K.IKEDA	
CHK.	4/JUL/95	APP.	4/JUL/95
Y.ISHIKAWA		S.MANABE	

コネクタ外形
OUTLINE OF HEADER HOUSING
12-φ1.1
DIA 1.1±0.1 12 PLACES
スルーホール 2-φ3
DIA 3±0.1 2 PLACES
ラウンド 2-φ4 MIN
ROUND DIA 4 MIN 2 PLACES

推奨基板取付け寸法
PC 基板厚: 1.6±0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN
PC BOARD THICKNESS: 1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

VIEW A
(SCALE: 1:1)

B ROW		X	Y		3-316081-5
A ROW					3-316081-3
B ROW		Y	Y		2-316081-5
A ROW					2-316081-3
B ROW		X	X		1-316081-5
A ROW					1-316081-3
					1-316081-2
KEYING LOCATION		A ROW KEYING	B ROW KEYING	FINISH	製品番号 PART NO.

TE Connectivity

WIRE RANGE	INSULATION DIA	NAME			
mm²(AWG)	mm	12 POS DOUBLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC D-3200			
MATERIAL	FINISH	一般公差 (GENERAL TOLERANCE)			
SEE NOTE 注記参照	SEE NOTE 注記参照	10mm 30mm 10mm 30mm 30mm 100mm	±0.3 ±0.4 ±0.45 角 度: ±3'	SIZE LOC NUMBER	SCALE REV. SHEET
				A3 J C-316081	2-1 B4 1 OF 1

(CUSTOMER DRAWING) 顧客用図面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-316081-2](#)