


OBSOLETE	OBSOLETE	OBSOLETE				<div><div></div><div>.624±.015</div><div></div></div>				
1	1	—	—	—	BUSHING	329058	POLYETHYLENE: (MIL-P-22748) TYPE I COLOR: NATURAL			
1	—	—	—	—	FERRULE	329041	COPPER (QQ-C-576) SILVER PL (QQ-S-365) .0002 MIN THK			
—	1	1	—	—		329056				
—	—	1	—	—	BUSHING	330576	POLYETHYLENE COLOR: YELLOW			
1	1	1	—	—	RETENTION SPRING	329042	BERYLLIUM COPPER (QQ-C-533) TIN PL (MIL-T-10727)			
1	1	1	1	—	CONNECTOR PIN	2-329009-1	<u>DIELECTRIC:</u> POLYPROPYLENE (MIL-T-3803) COLOR: TABLE II <u>SHELL:</u> BRASS (MIL-C-50) GOLD PL (MIL-G-45204) TYPE II .00003 MIN THK OVER NICKEL PL (QQ-N-290) .00003 MIN THK. <u>CONTACT:</u> BRONZE (ASTM-B140) GOLD PL (MIL-G-5204) TYPE II .00003 MIN THK OVER NICKEL PL (QQ-N-290) .00003 MIN THK.			
—	—	—	—	1		329009				
QTY					DESCRIPTION	PART NO.	MATERIAL & FINISH			
2-329009-6	2-329009-5	2-329009-3	2-329009-1	329009	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. LAUBACH	04OCT2005	<div><div><div></div></div><div><div>Tyco</div><div>Electronics</div></div><div>Tyco Electronics Corporation Harrisburg, Pa 17105-3608</div></div>	
					DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK G. MICHAEL	10-13-05		
						0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .008 4 PLC ± — ANGLES ± 5°	APVD G. MICHAEL	10-13-05	COAXICON CONNECTOR TWIN COAXIAL PLUG ASSEMBLY	
						MATERIAL SEE TABLE 1	FINISH —	PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		
					CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV N1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[329009](#)