



Index	Änderung	Tag	Name
A	BESCHRIFTUNG ANGEPAßT	21.5.81	JANOUSCH
E1	MATERIAL CHANGED, ENGLISH TEXT ADDED	9JAN08	ACK
E2	REVISED PER ECO-09-026444	28NOV09	KK
E3	ECR-10-026307	04FEB11	KK / HMR

FELD VERTIEFT  
BESCHRIFTUNG ERHABEN  
AREA RECESSED  
LETTERS RAISED



- 1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI  
2 OBSOLETE

ANREIHBARE AUSFÜHRUNG  
STACKABLE VERSION



STACKABLE VERSION											
ANREIHBARE AUSFÜHRUNG											
6-926 657-5	38,06	15	1-926 657-5	14x2,54=35,56	38,56	15					
6-4	35,52	14	1-4	13x2,54=33,02	36,02	14					
6-3	32,98	13	1-3	12x2,54=30,48	33,48	13					
6-2	30,44	12	1-2	11x2,54=27,94	30,94	12					
6-1	27,9	11	1-1	10x2,54=25,4	28,4	11					
6-0	25,36	10	1-0	9x2,54=22,86	25,86	10					
5-9	22,82	9		8x2,54=20,32	23,32	9					
5-8	20,28	8		7x2,54=17,78	20,78	8					
5-7	17,74	7		6x2,54=15,24	18,24	7					
5-6	15,2	6		5x2,54=12,7	15,7	6					
5-5	12,66	5		4x2,54=10,16	13,16	5					
5-4	10,12	4		3x2,54=7,62	10,62	4					
5-3	7,58	3		2x2,54=5,08	8,08	3					
5-2	5,04	2		1x2,54=2,54	5,54	2					
5-926 657-2	5,04	2	926 657-2	1x2,54=2,54	5,54	2					
ORDER NO.		POS.	ORDER NO.			POS.					
BESTELL NR.	C	POLZ	BESTELL NR	A	B	POLZ					

			<b>TE</b> TE Connectivity		
			Benennung		
SEE TABLE			LOCKING - CLIP GEHÄUSE		
ORDER NO.			LOCKING - CLIP HOUSING		
Bestell-Nr.			K		
Gez. 26.8.1980			Gepr. 4.9.80		
MATERIAL PBT 15% GV			COLOUR BLACK		
Werkstoff			Oberfläche Farbe		
Nicht tolerierte Maße			Format C		
± 0,2 mm			Zeichnungs-Nr. 926657		
Maßstab 5:1			REV. E3		
			Blatt-Nr.		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[926657-3](#)