

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2020

TE Connectivity Ltd.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	20JAN2020	AFK	LS

FLATTENED WIDTH

D

w

d

EXPANDED TUBING PRODUCT

SPOOL

SPOOL I.D. 101 (4.0)

Product Size	2.4	3.2	4.8	6.4	9.5	12.7	19.0	25.4	38.1
"D" Minimum Supplied I.D.	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.252)	9.50 (.374)	12.7 (.500)	19.0 (.748)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	1.20 (.047)	1.60 (.063)	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.4 (.252)	9.50 (.374)	12.7 (.500)	19.1 (.750)
"w" Recovered Wall Thickness	0.50±0.10 (.020±.004)	0.50±0.10 (.020±.004)	0.51±0.11 (.020±.004)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.75±0.15 (.030±.006)	0.90±0.15 (.035±.006)	1.00±0.20 (.039±.008)
Minimum Sleeve Flattened Width	5.90 (.232)	6.50 (.256)	8.90 (.350)	11.0 (.433)	15.7 (.618)	20.7 (.815)	30.7 (1.209)	41.1 (1.618)	61.0 (2.402)

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

0

1

2

3

4

PLC

± -

FINISH

-

DWN AFK 15JAN2020

CHK -

APVD LS 20JAN2020

PRODUCT SPEC RW-2072

APPLICATION SPEC -

WEIGHT VARIOUS

CUSTOMER DRAWING

TE

TE Connectivity

HX-CT

OUTSIDE PRINTER SPOOL

SIZE A3

CAGE CODE 0198G

DRAWING NO C-MCD170013

RESTRICTED TO -

SCALE -

SHEET 1 OF 1

REV 2

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8202-000](#)