



- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

High Speed Connectors

2mm Centerline Futurebus+ Connectors (Z-PACK 2mm FB)

AMP 5223123-1 **Active** [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 5223123-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info Sales Info Assembly Subcontractors	Pricing Product Availability	Tooling

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not relevant for lead free process
Module Type:	Signal
No. of Signal Positions:	390
Product Type:	Free-Board (Receptacle)
Sequencing:	No
PCB Mount Angle:	Right Angle
No. of Rows:	5
Termination Post Length (mm [in]):	3.56 [0.140]
Post Type:	Press-Fit
Post Plating:	Tin

Other Properties:	
RoHS/ELV Compliance History:	Always was compliant
Centerline, Matrix (mm [in]):	2.00 x 2.00 [.079 x .079]
Press-Fit Post Style:	Compliant
Contact Material:	Phosphor Bronze
Contact Mating Area Plating:	Gold Flash over Palladium Nickel
Housing Material:	Liquid Crystal Polymer (LCP)
Selectively Loaded:	Yes

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contain component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5223123-1](#)