

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
AJ		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A	REV PER ECO 06-02539	07APR06	GB	JH
					A1	REVISED PER ECO-09-024717	04NOV09	KK	AEG

Technical drawing of a plug assembly. The drawing shows a side view of the plug with various dimensions and callouts. The overall length is 33.73 MAX [1.328]. The diameter of the main body is Ø14.53 MAX [.572]. Callout 1 points to the plug body. Callout 2 points to the crimp end. Callout 3 points to the ferrule. Callout 4 points to the dielectric. Callout 5 points to the seal. A note indicates '7/16 WRENCH FLAT' for the ferrule.

1. USE PRO-CRIMPER 354940-1 WITH DIE SET 91909-1.

2. SEE INSTRUCTION SHEET 408-2055.

3. PARTS PACKAGED UNASSEMBLED.

4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4	OBSOLETE	ROLM 49D2401 TWINAX	332214	332222-1	9-332224-0	1-332221-5	5-330949-0	<del>5332225-6</del>
		RG 108/U & 108A/U	332214	332222-1	9-332224-0	1-332221-4	5-330949-0	5332225-5
4	OBSOLETE	TROMPETER TWC-124-2	332214	332222	9-332224-1	1-332221-3	2-330949-2	<del>5332225-3</del>
		RG 108/U & 108A/U	332214	332222	9-332224-1	332221	2-330949-2	5332225
		FOR USE WITH CABLE	5 SEAL QTY=1	4 DIELECTRIC QTY=1	3 FERRULE QTY=1	2 CRIMP END QTY=1	1 PLUG ASSY QTY=1	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

MATERIAL  
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± -  
4 PLC ± -  
ANGLES ± 1°  
FINISH -

DWN  
L. VARELA - DOCK5  
CHK  
J. HAVENER  
APVD  
J. LIPPERT  
PRODUCT SPEC  
-  
APPLICATION SPEC  
-  
WEIGHT  
0.50 OZ.

21APR2005  
21APR2005  
21APR2005

CUSTOMER DRAWING

Tyco Electronics Corporation  
Harrisburg, PA 17105-3608

NAME  
PLUG,  
TWIN BNC

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-5332225

RESTRICTED TO  
-

SCALE  
5:1

SHEET  
1 OF 1

REV  
A1

AMP 1470-19 REV 31MAR2000

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5332225](#)