


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	Contact material change from CuSn to CuZn	19SEP2017	KJK	PS


POS.	L±0.5	PART NUMBER
-	-	-
2	5.08	827312 -2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1-
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2-
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5- 827312 -0



NOTES:

- ① MIN. 3μm TIN OVER 1.27μm NICKEL  
② OBSOLETE

PIN HOUSING	PCT	BLACK	2
CONTACT PIN	CuZn	①	1
DESCRIPTION	MATERIAL	COLOR/FINISH	ITEM NUM

DIMENSIONS: mm	DWN KREPP 13.02.79	MATERIAL -	FINISH -
	CHK HOWEL 16.02.79	 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	APVD KOURIMSKY 09.04.81		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-18012	NAME AMPMODU II PIN HEADER SINGLE ROW	
	APPLICATION SPEC -	SIZE A4	CAGE CODE 00779
	WEIGHT	DRAWING NO C=827312	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
		REV E	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[827312-4](#)