



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TE PERSONNEL WITHOUT AUTHORIZATION FROM TE (www.te.com).

DRAWING NUMBER:
454651-ENV

B



C



D

NOTES:

- ITEM TO BE PACKED IN A PLASTIC BAG MARKER WITH A MINIMUM OF TE PART NUMBER AND DATE CODE
- FERRULE ASSEMBLY NOT SUPPLIED WITH CONNECTOR, SEE D456099-ENV
- MASTER KEYWAY ONLY FOR RSC00E-U-***. UNIVERSAL CONNECTOR INTERMATEABLE WITH ALL KEY VARIANTS ON RSC PLUG
- DATE CODE AND PART NUMBER: H9904D RSC00E - N - ***

E

DATE CODE
CONNECTOR TYPE:
RSC00E : 4 HOLE MOUNTING
RSC20E: 2 HOLE MOUNTING

KEY:
N, A, B, C, D, E, U

CABLE DIAMETER:

090 = Ø0.9mm
100 = Ø2.5mm
180 = Ø1.8mm
200 = Ø2.0mm
300 = Ø1.65mm
400 = Ø3.0mm
500 = Ø3.2mm
600 = Ø2.1mm
700 = Ø1.6mm (GLASS BRAID)
800 = Ø3.7mm
900 = Ø5.0mm

ITEM No	DESCRIPTION
1	RECEPTACLE SHELL
2	FRONT SEAL (FITTED)
3	RSC TERMINI (SEE NOTE 2)
4	SPRING
5	O-RING 4.0 X 1.25 (FITTED)
6	PLUG FERRULE CARRIER
7	O-RING 3.0 X 1.5(FITTED)
8	CABLE ADAPTOR
9	CRIMP SLEEVE
10	STRAIN RELIEF BOOT
11	HEATSHRINK SLEEVE

F

AA	DUK-71611	MJH	NPO	MJH	CP	20/05/2020
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE

1

2

3




4

5

6

7


8



A


B

RSC00E-*090 VARIANT, NO CRIMP SLEEVE, REDUCED DIAMETER CABLE ADAPTER



C

RSC00E-*800 AND RSC00E-*900 VARIANTS
STRAIGHT CRIMP SLEEVE AND HEAT SHRINK



D

E

BS8888 THIRD ANGLE PROJECTION 		MATERIAL: SEE TABLE		FINISH:		 DEUTSCH TE CONNECTIVITY UK LTD., ST. LEONARDS-ON-SEA, TN38 9RF, UK.	
UNLESS OTHERWISE STATED: DIMENSIONS: mm [INCHES]		TITLE: RSC RECEPTACLE ASSEMBLY		TYPE: CUSTOMER DRAWING			
IF IN DOUBT, ASK		SIZE: A3	SCALE: 1:1	DRAWING NUMBER: 454651-ENV		SHEET: 1 OF 1	ISSUE: AA

F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RSC00E-A-180](#) [RSC00E-N-180](#) [RSC00E-N-100](#) [RSC00E-A-100](#) [RSC00E-B-100](#) [RSC00E-C-100](#) [RSC00E-D-100](#)
[RSC00E-E-100](#) [RSC00E-U-280](#)