



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02MAR2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X



- NOTES:
- 1. TECHNICAL DATA: SEE TABLE 1
 - 2. STRIP AND RETAIN THE INSULATION
 - 3. RECOMMEND TORQUE 0.4Nm
 - 4. TE LABEL AREA.
 - 5. -*: CABLE LENGHT.-0.5:0.5m, -1.0:1.0m, -1.5:1.5m...
 - 6. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

- 注意事项
1. 技术参数：见表1
2. 剥线并保留绝缘层；
3. 推荐扭矩0.4Nm；
4. TE 标签位置；
5. -**线长：-0.5:0.5m, -1.0:1.0m, -1.5:1.5m
6. 产品必须符合ROHS与REACH.



-	BRASS	SHIELDING	7
-	-	CABLE	6
-	-	LABEL	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -**: 00.0m -001: **.5m	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-MR-4CON-PUR-**SH	5	4	T4061220004-00X
					RPC-M8-MR-3CON-PUR-**SH	5	3	T4061220003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-MR-4CON-PVC-**SH	5	4	T4061210004-00X
					RPC-M8-MR-3CON-PVC-**SH	5	3	T4061210003-00X
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE		POS.	PART NUMBER

TABLE 1		
TECHNICAL DATA	T40612X0003-00X	T40612X0004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 28JAN2016 Nick Pan	TE Connectivity M8 CABLE ASSEMBLY SHIELDED RIGHT ANGLE, MALE, SINGLE END TYPE			
DIMENSIONS:			CHK 28JAN2016 Kobby Zhao				
mm			APVD 28JAN2016 Xiang Xu				
TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC 108-106140				
0 PLC ±- 1 PLC ±0.50 2 PLC ±0.35 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH			APPLICATION SPEC -	SIZE A2	CAGE CODE -	DRAWING NO ©T40612X000X00X	RESTRICTED TO -
MATERIAL TBD			WEIGHT -	CUSTOMER DRAWING			
-			SCALE 1:1		SHEET 1	OF 1	REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4061220003-003](#)