


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	30DEC2016	DL	CW
	A1	ECR-16-018258	30DEC2016	BS	CW
	B	ECR-18-016391	22OCT2018	GY	CW
	C	ECR-20-014876	21JUL2021	WOR	CW

NOTES:



1. TECHNICAL CHARACTERISTICS:
HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY
HOUSING SURFACE: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释：

技术参数：
下壳材料： 铝合金
下壳表面处理： 灰色粉末喷涂
防护等级： IP65(配合)



PG/M
THREAD-2
螺纹孔-2




TI470241121-000	H24B-SGRHS-PG21	H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳, 表面安装, 不锈钢双扣, PG21, 高结构, 灰色粉末喷涂	PG21	-	TYPE I 类型I
TI470241129-000	H24B-SGRHS-PG29	H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳, 表面安装, 不锈钢双扣, PG29, 高结构, 灰色粉末喷涂	PG29	-	
TI470241132-000	H24B-SGRHS-M32	H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳, 表面安装, 不锈钢双扣, M32, 高结构, 灰色粉末喷涂	M32	-	
TI470241221-000	H24B-SGRHS-2PG21	H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳, 表面安装, 不锈钢双扣, 2PG21, 高结构, 灰色粉末喷涂	PG21	PG21	
TI470241229-000	H24B-SGRHS-2PG29	H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳, 表面安装, 不锈钢双扣, 2PG29, 高结构, 灰色粉末喷涂	PG29	PG29	
TI470241232-000	H24B-SGRHS-2M32	H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳, 表面安装, 不锈钢双扣, 2M32, 高结构, 灰色粉末喷涂	M32	M32	
PART NUMBER 料 号	PART DESCRIPTION 描 述		PG/M THREAD-1 螺 纹 孔 - 1	PG/M THREAD-2 螺 纹 孔 - 2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17JUN2015 DAVID LI CHK 17JUN2015 CHRIS WANG APVD 17JUN2015 XU XIANG PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME H24B-SGRHS-PG/M	
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		SIZE A2	
MATERIAL TBD -		- -		CAGE CODE -	
		CUSTOMER DRAWING		DRAWING NO C-T147024XXXX000	
				RESTRICTED TO REV C	
				SCALE 4:5	
				SHEET 1 OF 2	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TYPE 2: HIGH CONSTRUCTION + STELL LOCKING, OTHER SPEC REFER TO TYPE 1.
类型2：高结构+彩锌双扣，其他规格参照类型1。

NOTES:
SEE SHEET 1



T1470242121-000	H24B-SGRH-PG21	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG21，高结构，灰色粉末喷涂	PG21	-	-	TYPE 2 类型2
T1470242125-000	H24B-SGRH-M25	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M25, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，M25，高结构，灰色粉末喷涂	M25	-	-	
T1470242129-000	H24B-SGRH-PG29	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG29，高结构，灰色粉末喷涂	PG29	-	-	
T1470242132-000	H24B-SGRH-M32	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，M32，高结构，灰色粉末喷涂	M32	-	-	
T1470242221-000	H24B-SGRH-2PG21	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2PG21，高结构，灰色粉末喷涂	PG21	PG21	-	
T1470242225-000	H24B-SGRH-2M25	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2M25, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2M25，高结构，灰色粉末喷涂	M25	M25	-	
T1470242229-000	H24B-SGRH-2PG29	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2PG29，高结构，灰色粉末喷涂	PG29	PG29	-	
T1470242232-000	H24B-SGRH-2M32	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2M32，高结构，灰色粉末喷涂	M32	M32	-	
T1470242921-000	H24B-SGRH-PG21/PG29	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG21/PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG21/PG29，高结构，灰色粉末喷涂	PG21	PG29	-	
T1470242932-000	H24B-SGRH-PG29/M32	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG29/M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG29/M32，高结构，灰色粉末喷涂	PG29	M32	-	
T1470243216-000	H24B-SGRH-M32/M16	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M32/M16, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，M32/M16，高结构，灰色粉末喷涂	M32	M16	-	
T1470242229-001	H24B-SGRH-2PG29/M32	H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG29, BOTTOM ENTRY M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2PG29，底出M32，高结构，灰色粉末喷涂	PG29	PG29	M32	
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD-1 螺纹孔-1	PG/M THREAD-2 螺纹孔-2	PG/M THREAD-3 螺纹孔-3	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 17JUN2015	TE Connectivity			
DIMENSIONS: mm		CHK CHRIS WANG 17JUN2015				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD XU XIANG 17JUN2015	NAME H24B-SGRH-PG/M			
		PRODUCT SPEC 108-137013				
		APPLICATION SPEC 114-137013				
MATERIAL TBD	FINISH -	WEIGHT -	SIZE A2	CAGE CODE -	DRAWING NO C-T147024XXXX000	RESTRICTED TO
CUSTOMER DRAWING				SCALE 1:2	SHEET 2 OF 2	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1470241232-000](#)