


REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	24SEP2016	DW	CW
	B	ECR-20-016312	03JUN2021	BS	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

T19I0062140-009	H6BPR-TSH-M40-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M40, POWDER COATED,GREY H6BPR对角锁定侧出上壳M40 灰色	M40	
T19I0062132-009	H6BPR-TSH-M32-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M32, POWDER COATED,GREY H6BPR对角锁定侧出上壳M32 灰色	M32	
T19I0062129-009	H6BPR-TSH-PG29-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG29, POWDER COATED,GREY H6BPR对角锁定侧出上壳PG29 灰色	PG29	
T19I0062125-009	H6BPR-TSH-M25-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M25, POWDER COATED,GREY H6BPR对角锁定侧出上壳M25 灰色	M25	
T19I0062121-009	H6BPR-TSH-PG21-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG21, POWDER COATED,GREY H6BPR对角锁定侧出上壳PG21 灰色	PG21	
T19I0062120-009	H6BPR-TSH-M20-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M20, POWDER COATED,GREY H6BPR对角锁定侧出上壳M20 灰色	M20	
T19I0062116-009	H6BPR-TSH-PG16-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG16, POWDER COATED,GREY H6BPR对角锁定侧出上壳PG16 灰色	PG16	
T19I0061140-009	H6BPR-TSH-M40-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M40, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳M40 银白色	M40	
T19I0061132-009	H6BPR-TSH-M32-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M32, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳M32 银白色	M32	
T19I0061129-009	H6BPR-TSH-PG29-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG29, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳PG29 银白色	PG29	
T19I0061125-009	H6BPR-TSH-M25-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M25, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳M25 银白色	M25	
T19I0061121-009	H6BPR-TSH-PG21-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG21, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳PG21 银白色	PG21	
T19I0061120-009	H6BPR-TSH-M20-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M20, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳M20 银白色	M20	
T19I0061116-009	H6BPR-TSH-PG16-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG16, POWDER COATED,SILVER WHITE H6BPR对角锁定侧出上壳PG16 银白色	PG16	
T19I0060140-009	H6BPR-TSH-M40-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M40, POWDER COATED,BLACK H6BPR对角锁定侧出上壳M40 黑色	M40	
T19I0060132-009	H6BPR-TSH-M32-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M32, POWDER COATED,BLACK H6BPR对角锁定侧出上壳M32 黑色	M32	
T19I0060129-009	H6BPR-TSH-PG29-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG29, POWDER COATED,BLACK H6BPR对角锁定侧出上壳PG29 黑色	PG29	
T19I0060125-009	H6BPR-TSH-M25-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M25, POWDER COATED,BLACK H6BPR对角锁定侧出上壳M25 黑色	M25	
T19I0060121-009	H6BPR-TSH-PG21-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG21, POWDER COATED,BLACK H6BPR对角锁定侧出上壳PG21 黑色	PG21	
T19I0060120-009	H6BPR-TSH-M20-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M20, POWDER COATED,BLACK H6BPR对角锁定侧出上壳M20 黑色	M20	
T19I0060116-009	H6BPR-TSH-PG16-EMC-C	H6BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG16, POWDER COATED,BLACK H6BPR对角锁定侧出上壳PG16 黑色	PG16	
PART NUMBER 料 号	PART DESCRIPTION 描 述			PG/M THREAD PG/M 螺纹

THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN DAVID WANG 24SEP2016				TE Connectivity					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:								CHK CHRIS WANG 24SEP2016		APVD XIANG XU 24SEP2016		NAME H6BPR-TSH-PG/M-EMC-C					
mm		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±								PRODUCT SPEC 108-137191 APPLICATION SPEC 114-137191		SIZE A1		CAGE CODE -		DRAWING NO. ©=T19I006XXXXX09		RESTRICTED TO	
MATERIAL		FINISH								WEIGHT		SCALE 1:1		SHEET 1		OF 1		REV B	
										CUSTOMER DRAWING									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[H6BPR-TSH-M25-EMC-C](#)