




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
©	COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	21MAY2015	GY	CW
	A1	ECR-18-009564	14SEP2018	CD	CW
	B	ECR-20-011774	30APR2021	BS	CW

D


printed on 30 Apr 2021 15:24 (China Standard Time) from IE236667

A



NOTES:  
I. TECHNICAL CHARACTERISTICS:  
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY  
SURFACE TREATMENT: SEE TABLE  
DEGREE OF PROTECTION: IP68 (MATED)

注释  
I. 技术参数:  
壳体材料: 铝合金  
表面处理: 见表格  
防护等级: IP68 (配合)





D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Gino.Yao 21MAY2015	 TE Connectivity			
DIMENSIONS:		CHK Chris.Wang 21MAY2015				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Xiang.Xu 21MAY2015	NAME H6BPR-TSHC-PG/M			
	0 PLC	±-	PRODUCT SPEC			
	1 PLC	±-	108-137014			
	2 PLC	±-	APPLICATION SPEC			
	3 PLC	±-	114-137014			
MATERIAL	4 PLC	±-	WEIGHT			
	ANGLES	±-	-			
-	FINISH	-	Customer Drawing			
			SIZE A2	CAGE CODE -	DRAWING NO T191206XXXXX00	RESTRICTED TO -
			SCALE 1:1	SHEET 1	OF 2	REV B

D

C  
printed on 30 Apr 2021 15:24 (China Standard Time) from IE236667

B

A

4


3

2


1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

TYPE 1  
类型 I



TYPE 2: NO LOGO  
类型：无LOGO



THIS TYPE IS SAME AS TYPE 1, ONLY NO LOGO  
此类型同类型 I，只是无LOGO

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B

A

T1912062125-001	POWDER COATED, DEEP GRAY 表面喷涂, 深灰色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,DEEP GREY,NO LOGO H6BPR上壳,中部锁定,侧出M25,深灰色粉末喷涂,无LOGO	M25	TYPE 2 类型2
T1912062125-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,GREY H6BPR上壳,中部锁定,侧出M25,灰色粉末喷涂	M25	TYPE 1 类型 I
T1912062121-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,GREY H6BPR上壳,中部锁定,侧出PG21,灰色粉末喷涂	PG21	
T1912062120-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-M20	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,GREY H6BPR上壳,中部锁定,侧出M20,灰色粉末喷涂	M20	
T1912062116-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-PG16	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,GREY H6BPR上壳,中部锁定,侧出PG16,灰色粉末喷涂	PG16	
T1912061125-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出M25,银白色粉末喷涂	M25	
T1912061121-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出PG21,银白色粉末喷涂	PG21	
T1912061120-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出M20,银白色粉末喷涂	M20	
T1912061116-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-PG16	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出PG16,银白色粉末喷涂	PG16	
T1912060125-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出M25,黑色粉末喷涂	M25	
T1912060121-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出PG21,黑色粉末喷涂	PG21	
T1912060120-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-M20	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出M20,黑色粉末喷涂	M20	
T1912060116-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-PG16	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出PG16,黑色粉末喷涂	PG16	
PART NUMBER 料 号	SURFACE TREATMEN 表 面 处 理	PART DESCRIPTION 描 述		PG/M THREAD PG/M 螺纹	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Gino.Yao 21MAY2015	TE Connectivity		
DIMENSIONS: mm		CHK Chris.Wang 21MAY2015			
		APVD Xiang.Xu 21MAY2015	NAME H6BPR-TSHC-PG/M		
		PRODUCT SPEC 108-137014			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		APPLICATION SPEC 114-137014	SIZE A2	CAGE CODE -	DRAWING NO T191206XXXXX00
MATERIAL -		WEIGHT -	RESTRICTED TO -		
Customer Drawing			SCALE 1:1	SHEET 2 OF 2	REV B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1912061121-000](#)