






LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
		C		REVISED PER ECR-21-100678	08APR2021	SS	VS



POS.	DIM. A
2*6	39.70
2*5	33.70
2*4	27.70
2*3	21.70



NOTE

1. MATERIAL:
- LEVEL A: PA6, COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT), UL 94V-0
- LEVEL B: PBT, HOT WIRE IGNITION (HWI) VERSION ARE MOLDED IN A RESIN THAT COMPLIES WITH TE PENDING HOT WIRE IGNITION TEST AND ARE RECOMMENDED FOR USE WITH HWI HOUSINGS THAT ALSO COMPLY, UL 94V-0


2. MATERIAL MARK:
- LEVEL A:GWT,LEVEL B:HWT

3. APPLICABLE CONTACT P/N
- RECEPTACLE CONTACT:1971237/1971779/81/83/85/87-*,2238066-*


4. MATING CONN, P/N
- CAP HSG: *-2232359/264-*
- TPA: *-1971778-*

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TOMMY WU	26MAR2013	TE Connectivity		
		CHK	HAPYE WU	26MAR2013			
		APVD	YUJHONG MAO	26MAR2013	NAME		
DIMENSIONS:					PRODUCT SPEC		
mm					108-106118		
					APPLICATION SPEC		
					114-106118		
					WEIGHT		
MATERIAL					Customer Drawing		
					SCALE		
					SHEET 1 OF 2		
					REV C		


LOC		DIST		REVISONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




2*5 POSITIONS




KEYING FOR 2*5 POS.




2*4 POSITIONS




KEYING FOR 2*4 POS.




2*3 POSITIONS



KEYING FOR 2*3 POS.



2*6 POSITIONS



KEYING FOR 2*6 POS.

2*6	LEVEL A	DARK GREY	KEY A	5-2232266-6
		BROWN	KEY B	6-2232266-6
		GREEN	KEY C	7-2232266-6
		ORANGE	KEY D	8-2232266-6
2*5	LEVEL A	DARK GREY	KEY A	5-2232266-5
		BROWN	KEY B	6-2232266-5
		GREEN	KEY C	7-2232266-5
		ORANGE	KEY D	8-2232266-5
POS.	MATERIAL	COLOR	KEY	P/N

2*4	LEVEL A	DARK GREY	KEY A	5-2232266-4
		BROWN	KEY B	6-2232266-4
		GREEN	KEY C	7-2232266-4
		ORANGE	KEY D	8-2232266-4
2*3	LEVEL A	BLACK	KEY A	1-2232266-4
		DARK GREY	KEY A	5-2232266-3
		BROWN	KEY B	6-2232266-3
		GREEN	KEY C	7-2232266-3
2*3	LEVEL B	ORANGE	KEY D	8-2232266-3
		BLACK	KEY A	1-2232266-1
POS.	MATERIAL	COLOR	KEY	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN TOMMY_WU 26MAR2013
CHK HAPYE_WU 26MAR2013
APVD YUJHONG_MAO 26MAR2013

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.35
1 PLC ±0.25
2 PLC ±0.25
3 PLC ±0.25
4 PLC ±0.25
ANGLES ±0.5°
FINISH

MATERIAL

-

Customer Drawing

SCALE

SHEET 2 OF 2

REV C

TE Connectivity

NAME

PLUG HOUSING, DOUBLE ROW
POWER TRIPLE LOCK

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A100779

2232266

-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-2232266-4](#)