





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		PER ECO-18-020143	31DEC2018	MY	GF
B		REVISED PER ECO-19-007907	24MAY2019	AP	GF
C		REVISED PER ECO-21-005293	01MAY2021	KK	AK



△ LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -6): -1 SHOWN



△ LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -44): -41 SHOWN



△ DASH NUMBER 41 THRU 44 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

- SEE SHEET 2 FOR WIRING SCHEMATIC.
- PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
- CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.

△ TEST IN ACCORDANCE WITH IEEE802.3bj.

△ LABEL INFORMATION: P1 SHOWN





△ SEE SHEET 2 FOR 2334236-1 AND 4-2334236-1 LABEL PLACEMENT.

9	30	700 ±25	2000 +80/-0	4-2334236-4
	30	500 ±25	1500 +50/-0	4-2334236-3
	30	330 ±25	1000 +50/-0	4-2334236-2
	30	120 ±12	500 +50/-0	4-2334236-1
	30	1000 ±25	3000 +80/-0	2334236-6
5	30	1000 ±25	2500 +80/-0	2334236-5
	30	700 ±25	2000 +80/-0	2334236-4
	30	500 ±25	1500 +50/-0	2334236-3
	30	330 ±25	1000 +50/-0	2334236-2
	30	120 ±12	500 +50/-0	2334236-1
STANDARD	GAGE	"L2"	"L1"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M YI 11APR2018	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK G. FRANKLIN 11APR2018		
DIMENSIONS:		APVD G. FRANKLIN 11APR2018	NAME	
mm		PRODUCT SPEC	CABLE ASSEMBLY, QSPF28 TO (4) SFP+	
	0 PLC ±	APPLICATION SPEC	SIZE	
	1 PLC ±		CAGE CODE	
	2 PLC ±		DRAWING NO	
	3 PLC ±		RESTRICTED TO	
	4 PLC ±		A100779C=2334236	
MATERIAL	FINISH	WEIGHT	RESTRICTED CUSTOMER	
			SCALE 5:4 SHEET 1 OF 2 REV C	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



2334236-1 & 4-2334236-1
LABEL PLACEMENT DETAIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. YI	11APR2018	TE Connectivity	
DIMENSIONS:		CHK G. FRANKLIN	11APR2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G. FRANKLIN	11APR2018	NAME CABLE ASSEMBLY, QSFP28 TO (4) SFP+	
	0 PLC	±	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO. RESTRICTED TO	
	1 PLC	±	APPLICATION SPEC		
	2 PLC	±	WEIGHT		
	3 PLC	±	RESTRICTED CUSTOMER		
MATERIAL	FINISH	ANGLES		A100779C=2334236	
				SCALE 3:2 SHEET 2 OF 2 REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2334236-1](#)