




- 1 GOLD FLASH OVER 0.00127[.000050] NICKEL,.000762[.000030] GOLD ON CONTACT AREA.
- 2 GOLD FLASH OVER 0.00127[.000050] NICKEL,.000381[.000015] GOLD ON CONTACT AREA.
- 3 PREPLATED .00127-.00381 (.000050-.000150) BRIGHT TIN.
- 4 REELED FOR MINI APPLICATOR.
- 5 GOLD PLATING NOT REQUIRED - THIS AREA.
- 6 REELED FOR STANDARD APPLICATOR
- 7 0.000127[.000050] NICKEL OVER ENTIRE CONTACT, 0.000381[.000015] GOLD IN CONTACT AREA.
- 8 SHEARED EDGES ARE PERMITTED TO BE UNPLATED.
- 9 CUT OUTS ON BOX AT MANUFACTURER'S OPTION.
- 10 0.000381[.000015] GOLD IN CONTACT AREA. 0.00254-0.00508[.000100-.000200] BRIGHT TIN-LEAD IN AREA L, ALL OVER 0.000127[.000050] NICKEL.
- 11 0.000762[.000030] GOLD IN CONTACT AREA. 0.00254-0.00508[.000100-.000200] BRIGHT TIN-LEAD IN AREA L, ALL OVER 0.000127[.000050] NICKEL.
- 12 OBSOLETE PART NUMBER.
- 13 POINT OF MEASUREMENT FOR PLATING THICKNESS(INSIDE BEAMS).
- 14 0.000127[.000050] NICKEL OVER ENTIRE CONTACT, 0.000762[.000030] GOLD IN CONTACT AREA.
- 15 .000015 GOLD IN CONTACT AREA. .000100-.000200 BRIGHT TIN IN AREA L, ALL OVER .000050 NICKEL.
- 16 0.000762[.000030] GOLD IN CONTACT AREA. 0.00254-0.00508[.000100-.000200] MATTE TIN IN AREA L, ALL OVER 0.000127[.000050] NICKEL.

	LOOSE PIECE		6-87523-9
	REELED		6-87523-8
	LOOSE PIECE		2-87523-4
	REELED		2-87523-3
	REELED		2-87523-2
	REELED		2-87523-1
	LOOSE PIECE		1-87523-9
	REELED		1-87523-8
	LOOSE PIECE		1-87523-6
	REELED		1-87523-5
	LOOSE PIECE		1-87523-4
	REELED		1-87523-3
	REELED		1-87523-0
	REELED		87523-9
	REELED		87523-8
	LOOSE PIECE		87523-7
	LOOSE PIECE		87523-6
	REELED		87523-5
	REELED		87523-4
	LOOSE PIECE		87523-3
	REELED		87523-2
DESCRIPTION		FINISH	PART NUMBER

17 OBSOLETE PARTS: OBSOLETE CIS STREAMLININGPERD.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.BRANDBERG 5-5-94	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK B. STAUCH 5-5-94		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B.STAUCH 5-5-94	NAME	
0 PLC ± -		PRODUCT SPEC	CONTACT, MOD IV	
1 PLC ± -		APPLICATION SPEC	CRIMP SNAP-IN RECEPTACLE	
2 PLC ± 0.13[.005]			SIZE	CAGE CODE
3 PLC ± -			DRAWING NO	RESTRICTED TO
4 PLC ± -			A2 00779	87523
ANGLES ± -		WEIGHT -	SCALE 10:1	SHEET 1 of 1
FINISH		CUSTOMER DRAWING	REV U2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-87523-1](#)