




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	19NOV2014	DW	CW
	A1	ECR-17-016096	01NOV2017	CH	CW
	A2	ECR-18-000021	03JAN2018	CH	CW
	B	ECR-20-014876	10NOV2020	WOR	CW

注释：
1. 技术参数：
上壳材料：铝合金
表面处理：灰色粉末涂层
防护等级：IP65（配合）



SCALE 1:2



TI270247121-000	H24B-TSBHS-PG21	H24B HOOD, SIDE ENTRY PG21, STAINLESS STEEL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED WITH INSIDE AND OUTSIDE, GREY H24B上壳, 侧出PG21, 不锈钢双扣, 高结构, 灰色粉末里外喷涂	PG21
TI270243140-000	H24B-TSBHS-M40	H24B HOOD, SIDE ENTRY M40, STAINLESS STEEL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出M40, 不锈钢双扣, 高结构, 灰色粉末喷涂	M40
TI270243132-000	H24B-TSBHS-M32	H24B HOOD, SIDE ENTRY M32, STAINLESS STEEL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出M32, 不锈钢双扣, 高结构, 灰色粉末喷涂	M32
TI270243129-000	H24B-TSBHS-PG29	H24B HOOD, SIDE ENTRY PG29, STAINLESS STEEL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出PG29, 不锈钢双扣, 高结构, 灰色粉末喷涂	PG29
TI270243125-000	H24B-TSBHS-M25	H24B HOOD, SIDE ENTRY M25, STAINLESS STEEL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出M25, 不锈钢双扣, 高结构, 灰色粉末喷涂	M25
TI270243121-000	H24B-TSBHS-PG21	H24B HOOD, SIDE ENTRY PG21, STAINLESS STEEL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出PG21, 不锈钢双扣, 高结构, 灰色粉末喷涂	PG21
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD PG/M 螺纹孔

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19NOV2014 DAVID.WANG		 TE Connectivity	
		CHK 19NOV2014 CHRIS.WANG			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME H24B-TSBHS-PG/M	
		APVD 19NOV2014 XIANG.XU		PRODUCT SPEC 108-137013	
				APPLICATION SPEC 114-137013	
				SIZE A2	
MATERIAL - -		FINISH - -		CAGE CODE -	
		WEIGHT -		DRAWING NO C-T12702431XX000	
		Customer Drawing		RESTRICTED TO -	
				SCALE 1:1	
				SHEET OF 1	
				REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1270243121-000](#)