




D




C





TYPE 1: H48B HOOD, NO ENTRY,2 EAR

类型1：H48B上壳，无线孔，2耳




TYPE 2: H48B HOOD, SIDE ENTRY,2 EAR
OTHER SPEC REFER TO TYPE 1

类型2：H48B上壳，侧出，2耳
未注规格参照类型1




TYPE 3: H48B HOOD, TOP ENTRY,2 EAR
OTHER SPEC REFER TO TYPE 1

类型3：H48B上壳，顶出，2耳
未注规格参照类型1




TYPE 6: H48B HOOD, TOP ENTRY (4 HOLE),2 EAR
OTHER SPEC REFER TO TYPE 1

类型6：H48B上壳，顶出(4孔)，2耳
未注规格参照类型1



TYPE 4: H48B HOOD, SIDE/TOP ENTRY,2 EAR
OTHER SPEC REFER TO TYPE 1&TYPE 2

类型4：H48B上壳，侧顶出，2耳
未注规格参照类型1和类型2



TYPE 7: H48B HOOD,SIDE ENTRY(2 HOLE),2 EAR
OTHER SPEC REFER TO TYPE 1

类型7：H48B上壳，侧出(2孔)，2耳
未注规格参照类型1

NOTES:

- TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释:

- 技术参数：
主体材料： 铝合金
表面处理： 灰色粉末喷涂
防护等级： IP65(配合)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A2		ECR-17-002665	27FEB2017	BS	CW
A3		ECR-18-018974	04DEC2018	WOR	CW
A4		ECR-19-010616	08JUL2019	CD	CW
B		ECR-21-109004	19AUG2021	WOR	CW


B

T10X0480000-000	H48B-TG/S-RO-XX	H48B HOOD, NO ENTRY, 2 EAR, POWDER COATED, GREY H48B上壳,无线孔,2耳,灰色粉末喷涂	-	-	-	TYPE 1
T1310480125-000	H48B-TS-RO-M25	H48B HOOD, SIDE ENTRY M25, 2 EAR, POWDER COATED, GREY H48B上壳,侧出M25,2耳,灰色粉末喷涂	M25	-	-	TYPE 2
T1310480129-000	H48B-TS-RO-PG29	H48B HOOD, SIDE ENTRY PG29, 2 EAR, POWDER COATED, GREY H48B上壳,侧出PG29,2耳,灰色粉末喷涂	PG29	-	-	
T1310480132-000	H48B-TS-RO-M32	H48B HOOD, SIDE ENTRY M32, 2 EAR, POWDER COATED, GREY H48B上壳,侧出M32,2耳,灰色粉末喷涂	M32	-	-	
T1310480136-000	H48B-TS-RO-PG36	H48B HOOD, SIDE ENTRY PG36, 2 EAR, POWDER COATED, GREY H48B上壳,侧出PG36,2耳,灰色粉末喷涂	PG36	-	-	
T1310480140-000	H48B-TS-RO-M40	H48B HOOD, SIDE ENTRY M40, 2 EAR, POWDER COATED, GREY H48B上壳,侧出M40,2耳,灰色粉末喷涂	M40	-	-	
T1310480142-000	H48B-TS-RO-PG42	H48B HOOD, SIDE ENTRY PG42, 2 EAR, POWDER COATED, GREY H48B上壳,侧出PG42,2耳,灰色粉末喷涂	PG42	-	-	
T1310480148-000	H48B-TS-RO-PG48	H48B HOOD, SIDE ENTRY PG48, 2 EAR, POWDER COATED, GREY H48B上壳,侧出PG48,2耳,灰色粉末喷涂	PG48	-	-	TYPE 3
T1310480150-000	H48B-TS-RO-M50	H48B HOOD, SIDE ENTRY M50, 2 EAR, POWDER COATED, GREY H48B上壳,侧出M50,2耳,灰色粉末喷涂	M50	-	-	
T1320480129-000	H48B-TG-RO-PG29	H48B HOOD, TOP ENTRY PG29, 2 EAR, POWDER COATED, GREY H48B上壳,顶出PG29,2耳,灰色粉末喷涂	-	PG29	-	
T1320480132-000	H48B-TG-RO-M32	H48B HOOD, TOP ENTRY M32, 2 EAR, POWDER COATED, GREY H48B上壳,顶出M32,2耳,灰色粉末喷涂	-	M32	-	
T1320480136-000	H48B-TG-RO-PG36	H48B HOOD, TOP ENTRY PG36, 2 EAR, POWDER COATED, GREY H48B上壳,顶出PG36,2耳,灰色粉末喷涂	-	PG36	-	
T1320480140-000	H48B-TG-RO-M40	H48B HOOD, TOP ENTRY M40, 2 EAR, POWDER COATED, GREY H48B上壳,顶出M40,2耳,灰色粉末喷涂	-	M40	-	
T1320480142-000	H48B-TG-RO-PG42	H48B HOOD, TOP ENTRY PG42, 2 EAR, POWDER COATED, GREY H48B上壳,顶出PG42,2耳,灰色粉末喷涂	-	PG42	-	TYPE 4
T1320480150-000	H48B-TG-RO-M50	H48B HOOD, TOP ENTRY M50, 2 EAR, POWDER COATED, GREY H48B上壳,顶出M50,2耳,灰色粉末喷涂	-	M50	-	
T1320480163-000	H48B-TG-RO-M63	H48B HOOD, TOP ENTRY M63, 2 EAR, POWDER COATED, GREY H48B上壳,顶出M63,2耳,灰色粉末喷涂	-	M63	-	
T13204804040-000	H48B-TG/TS-RO-M40/M40	H48B HOOD, TOP/SIDE ENTRY M40, 2 EAR, POWDER COATED, GREY H48B上壳,顶/侧出M40,2耳,灰色粉末喷涂	M40	M40	-	
T1320485040-000	H48B-TG/TS-RO-M50/M40	H48B HOOD, TOP ENTRY M50, SIDE ENTRY M40, 2 EAR, POWDER COATED, GREY H48B上壳,顶出M50,侧出M40,2耳,灰色粉末喷涂	M40	M50	-	
T1320480225-000	H48B-TG-RO-2M25	H48B HOOD, TOP ENTRY 2M25, 2 EAR, POWDER COATED, GREY H48B上壳,顶出2M25,2耳,灰色粉末喷涂	-	2X M25	-	TYPE 5
T1320482520-000	H48B-TG-3M25M20	H48B HOOD, TOP ENTRY 3M25, 1M20, 2 EAR, POWDER COATED, GREY H48B上壳,顶出3M25,1M20,2耳,灰色粉末喷涂	-	3X M25	M20	TYPE 6
T1310480229-000	H48B-TS-RO-2PG29	H48B HOOD, SIDE ENTRY 2PG29,2 EAR, POWDER COATED, GREY H48B上壳,侧出2PG29,2耳,灰色粉末喷涂	PG29	PG29	-	TYPE 7
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD-1 螺纹孔-1	PG/M THREAD-2 螺纹孔-2	PG/M THREAD-3 螺纹孔-3	TYPE 类型

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 08JUN2015	 TE Connectivity	
DIMENSIONS:		CHK CHRIS WANG 08JUN2015		
mm		APVD XU XIANG 08JUN2015	NAME H48B-TG/TS-RO-PG/M	SIZE A1
		PRODUCT SPEC		
		108-137013	CAGE CODE -	DRAWING NO C= T13X048XXXX000
		APPLICATION SPEC		
114-137013		RESTRICTED TO -		
MATERIAL -				
FINISH -		WEIGHT -	REV B	
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1310480129-000](#)