


4

3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		F	REDRAWN W/CHANGE	ECR-09-016911	30JUL09	TS KB



1. -A- 面より2mmの範囲で測定。
2. 相手ハウジングと所定の機能を満たして嵌合できること。
3. 適用リセプタクルコンタクト型番：170177, 170286
4. 適用製品規格番号：108-5093, 108-5099
5. 相手ハウジングとの嵌合力は29.4N (3Kg) 以下、
但し、コンタクトは含まない。
1. TO BE MEASURED WITHIN 2mm FROM -A-
2. IN COUPLING WITH THE PLUG HOUSING
MATING SATISFIES FUNCTION.
3. APPLIDE CONTACTPART NUMBER：170177, 170286
4. PRODUCT SPECIFICATION NUMBER：108-5093, 108-5099
5. IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N (3Kg) MAX. WITHOUT REC CONTACTS.

OBSOLETE	黄 / YELLOW	171358-7
OBSOLETE	灰 / GRAY	171358-6
OBSOLETE	青 / BLUE	171358-5
	緑 / GREEN	171358-4
OBSOLETE	茶 / BROWN	171358-3
	黒 / BLACK	171358-2
	自然色 / NATURAL	171358-1
	色 / COLOR	型番 / PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 30JUL09	Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: mm		CHK K.BETSUI 30JUL09				
		APVD K.BETSUI 30JUL09	NAME MULTI-INTERLOCK CONNECTOR 13POSITION PLUG HOUSING			
		PRODUCT SPEC SEE NOTE 4				
MATERIAL 66 NYLON		FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-171358
GENERAL TOLERANCE 10 ≥ : ±0.2 30 ≥ > 10 : ±0.25 100 ≥ > 30 : ±0.3 ANGLE : ±3°		CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[171358-4](#) [171358-1](#)