



.039	.230	.426	.534	.605	2.178	2.635	2.406	.441	2.079	50	1-2157480-5
[0.99]	[5.84]	[10.82]	[13.56]	[15.37]	[55.32]	[66.93]	[61.11]	[11.20]	[52.81]		
.039	.230	.426	.422	.494	2.272	2.729	2.500	.329	2.182		
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[57.71]	[69.32]	[63.50]	[8.36]	[55.42]	37	1-2157480-4
.039	.230	.426	.422	.494	1.625	2.088	1.852	.329	1.534		
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[41.27]	[53.03]	[47.04]	[8.36]	[39.96]		
.030	.235	.422	.422	.494	1.083	1.541	1.312	.329	.994	15	1-2157480-2
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[27.51]	[39.14]	[33.32]	[8.36]	[25.25]		
.030	.235	.422	.422	.494	.759	1.213	.984	.329	.666		
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[19.28]	[30.81]	[24.99]	[8.36]	[16.92]	9	1-2157480-1
.039	.230	.426	.534	.605	2.178	2.635	2.406	.441	2.079		
[0.99]	[5.84]	[10.82]	[13.56]	[15.37]	[55.32]	[66.93]	[61.11]	[11.20]	[52.81]		
.039	.230	.426	.422	.494	2.272	2.729	2.500	.329	2.182	37	2157480-4
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[57.71]	[69.32]	[63.50]	[8.36]	[55.42]		
.039	.230	.426	.422	.494	1.625	2.088	1.852	.329	1.534		
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[41.27]	[53.03]	[47.04]	[8.36]	[39.96]	25	2157480-3
.030	.235	.422	.422	.494	1.083	1.541	1.312	.329	.994		
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[27.51]	[39.14]	[33.32]	[8.36]	[25.25]		
.030	.235	.422	.422	.494	.759	1.213	.984	.329	.666	9	2157480-1
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[19.28]	[30.81]	[24.99]	[8.36]	[16.92]		
DIM K	DIM J	DIM H	DIM G	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. C.C. THOMAS 10-14-14		 TE Connectivity	
		CHK. C. DERRICK 10-14-14			
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		C. DERRICK 10-14-14		PLUG ASSY, SIZE 1-5, IP67 SERIES 109, AMPLITUDE WITH IF SEAL AND GROMMET	
		APPRO. C. DERRICK			
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL		WEIGHT		SIZE	CAGE CODE
SEE CALLOUTS		0.000000		A1	00779
FINISH		CUST. DRAWING		DRAWING NO.	
SEE CALLOUTS				C-2157480	
				SCALE	SHEET
				4:1	1 OF 1
				REV	F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2157480-2](#) [1-2157480-5](#)