




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B6	REVISED PER ECN-22-162091	07JUL2022	WLS	VS
	B7	REVISED PER ECN-23-242776	14DEC2023	WLS	VS



- 1 MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 RETENTION BUMP FEATURES FACE EACH OTHER, TYPICAL ALL CONFIGURATIONS.
- 4 PLATING: CONTACTS - 0.76µm MINIMUM GOLD ON MATING AREA.
2.54µm MINIMUM MATTE TIN ON SOLDER TAILS.
ALL OVER 1.27µm MINIMUM NICKEL.
- 5 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACCORDING TO NUMBER OF POSITION).
- 6 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.
- 7 CUTTING EDGE, NO PLATING PRESENT IN THE REGION SHOWN.



OBSOLETE	12,11,2,1	33.00	39.14	37.00	12	3-1445093-2
OBSOLETE	11,10,3,2	30.00	36.14	34.00	11	3-1445093-1
	10,9,2,1	27.00	33.14	31.00	10	3-1445093-0
	9,8,3,2	24.00	30.14	28.00	9	2-1445093-9
	8,7,2,1	21.00	27.14	25.00	8	2-1445093-8
OBSOLETE	7,6,3,2	18.00	24.14	22.00	7	2-1445093-7
	6,5,2,1	15.00	21.14	19.00	6	2-1445093-6
	5,4,3,2	12.00	18.14	16.00	5	2-1445093-5
	4,3,2,1	9.00	15.14	13.00	4	2-1445093-4
	3,2	6.00	12.14	10.00	3	2-1445093-3
	2,1	3.00	9.14	7.00	2	2-1445093-2
	CON POS W/RET BUMP 3	DIM Z	DIM V	DIM L	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.ROOT 10OCT2000	TE Connectivity			
DIMENSIONS: mm		CHK K.WHLAKER 17-APR-2001				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C.JONES 17-APR-2001	NAME VERTICAL THRU HOLE HEADER ASSY, 0.76 MIC GOLD CONTACTS, W/PCB PLZN FEATURE, SGL ROW, MICRO MATE-N-LOK(TM)			
0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000				
MATERIAL 1		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-1445093	RESTRICTED TO -
4		CUSTOMER DRAWING	SCALE 4:1	SHEET 1	OF 2	REV B7


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B

A




PCB LAYOUT COMPONENT SIDE

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT	10OCT2000	 TE Connectivity					
DIMENSIONS:		CHK K. WHITAKER	17-APR-2001						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES	17-APR-2001	NAME VERTICAL THRU HOLE HEADER ASSY, 0.76 MIC GOLD CONTACTS, W/PCB PLZN FEATURE, SGL ROW, MICRO MATE-N-LOK(TM)					
mm		PRODUCT SPEC							
		108-1836		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		APPLICATION SPEC		A200779C-1445093					
		114-13000							
MATERIAL		WEIGHT		-					
-		CUSTOMER DRAWING		SCALE	4:1	SHEET	2 OF 2	REV	B7
-									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1445093-6](#)