



a) Supplied profile.

b) Recovered profile.



S1112 ADHESIVE



MATERIAL;

Section: Heat-shrinkable, thermally stabilised, irradiated, flame retarded Polyolefin.

Adhesive: Raychem hot-melt adhesive S1112

Properties to conform to Raychem Specification RK6182

DIMENSIONS (in millimetres)

PART No.	A	B	C	D	E
	MAX	MIN	MIN	MIN	TYP
	b	b	b	a	b
Nr. 6	0.6	0.5	3.5	0.8	1.25
Nr. 7	1.0	0.9	4.8	1.6	1.25
Nr. 8	2.0	0.9	6.6	2.5	2.25
Nr. 9	4.2	0.9	13.5	4.5	2.20
OBSOLETE Nr. 11	1.5	0.8	4.9	1.6	1.35
Nr. 12	3.2	0.8	6.0	5.0	1.15

NOTE.

- 1) Standard supplied length is 1.2 metres.
- 2) Standard colour is black.
- 3) Also available in white.
- 4) "D" Only applicable to unmodified 1.2 metre lengths.

Copyright (!)

Urheberrechte

The copyright in this drawing is the property of Raychem Ltd. The drawing is issued on condition that it is not copied, reproduced or disclosed to a third party, either in whole or in part without the prior written consent of Raychem Ltd.

Drawn A.LILLEY

Checked *[Signature]*

Issue 16

Date 11MAY11

Conforms to ISO Recommendations
3rd Angle Projection
Not to Scale

Approval
Design *[Signature]*

03.08.98

MKTG. *[Signature]*

G.A. *[Signature]*



Iss.	Date	E.C.R. No.	Details of Change
2	January 1986	4946/7	Dim changed
3	January 1986	4993/4	Dim changed
4	December 1986	4957	Coat machine
5	June 1987	5094	Conform to RK
6	February 1988	5246	Change D dim
7	August 1988	5334	New size 11
8	July 1991	T0067	Bought in line with UKMS
9	March 1992	T0112	Nr 9 D dim was 4mm
10	June 1993	T0208	Nr 9 D dim was 7mm
11	August 1995	T0424	Nr12 added
12	April 1995	T0416	Nr7 also in white
13	December 1995	T0427	Bought in lin ewith UKMS & data\$
14	May 1998	CRF-T465	Note 4 added
15	June 1998	CR98-HP-0007	RK was 6029
16	11MAY11	ECR-10-026388	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RAYRIM-NR9-0-SP](#)