

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2009

© COPYRIGHT 2009

BY -


ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	ECR-09-023155	22OCT2009	VG	AR
	A6	ECR-10-009777	17MAY2010	SR	AR
	B	ECR-16-001983	20MAY2016	GCM	JB
	C	ECR-16-014579	10MAY2017	GCM	JB

Notes

- 1 SUITABLE HOUSINGS: SERIES EMV, SIZE 1
CUSTOMER DRAWING 1102700, 1106402, 1106200
- 2 STANDARDS:
DIN EN 61984, DIN EN 60664-1
- 3 SUR TEC 650 CHROMIT AL TCP PASSIVATION
- 4 TOOL:
PHILLIPS SCREWDRIVER PH1.
- 5 VARNISH ON INSIDE AREA NOT NECESSARY
- 6 PACKAGING:
10 SETS IN A CARTON.



PN 0-1 AS SHOWN

1					ANGLED BULKHEAD HOUSING		ALU	BLACK	SERIES EMV-K WITHOUT LOGO	8
1	1	1	1	1	SCREW COUNTERSUNK RAISED HEAD	-	STAINL. STEEL V2A	-	M3x8 PH1 DIN EN ISO 7047	7
1	1	1	1	1	O - RING	-	NBR	BLACK	3.0x1.0	6
1	1	1	1	1	PROGFILE SEAL	-	FKM	BLACK	SERIES EMV / HIP	5
	-	1	-	-	ANGLED BULKHEAD HOUSING	M20	ALU	BLACK SEE NOTE 3	SERIES EMV-K	4
	1	-	-	-	ANGLED BULKHEAD HOUSING	M20	ALU	GREY	SERIES EMV-K	3
	-	-	1	-	ANGLED BULKHEAD HOUSING	M16	ALU	BLACK SEE NOTE 3	SERIES EMV-K	2
	-	-	-	1	ANGLED BULKHEAD HOUSING	M16	ALU	GREY	SERIES EMV	1
0-5	0-4	0-3	0-2	0-1		"A"	MATERIAL	COLOR/SURFACE	NOTE	ITEM
PN/QTY					DESCRIPTION					

PARTS LIST (PER ONE UNIT)

0-5	EMV-K.3/4.SG-N
0-4	EMV.3/4.SG.1.M20.G
0-3	EMV-K.3/4.SG.1.M20.G
0-2	EMV-K.3/4.SG.1.M16.G
0-1	EMV.3/4.SG.1.M16.G
PART NO.	ORDERING TEXT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±1°
MATERIAL	FINISH
-	-

DWN	V.GLUMM	26AUG2009
CHK	H.Braun	26AUG2009
APVD	T.Schnurpfel	26AUG2009
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		



TE Connectivity

NAME
ANGLED BULKHEAD HOUSING ASS'Y
SIDE ENTRY, SERIES EMV, SIZE 1

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1106401	-

SCALE	SHEET	1 OF 1	REV
1:1			C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1106401-3](#)