

35610 ✓ ACTIVE

SOLISTRAND | SOLISTRAND Budget


TE Internal #: 35610

SOLISTRAND Budget, Knife Disconnects, Silver, Knife Disconnect,
22 – 16AWG Wire Size, .26 – 1.65mm² Wire Size, .51 – 3.26kcmil
Wire Size, Loose Piece

[View on TE.com >](#)



Terminals & Splices > Knife Disconnects



Body Plating Material: **Silver**

Wire Insulation Support: **Without**

Terminal & Splice Type: **Knife Disconnect**

Wire Size: **.26 – 1.65 mm²**

Features

Product Type Features

Sealable	No
Insulated	No

Body Features

Body Plating Material	Silver
-----------------------	--------

Contact Features

Terminal & Splice Type	Knife Disconnect
------------------------	------------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.51 – 3.26 kcmil
-----------	------------------

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | [SOLISTRAND Budget](#)



Knife Disconnects(4)



Rings & Spades(181)



Splices(1)

Customers Also Bought



TE Part #T2111252101-007
HDC HMN - RAIL COMPLIANT
MODULAR SYSTEM



TE Part #2340326-1
ASSY STRADDLE MOUNT 84P 062
SLIVER 2.0



TE Part #2-342104-1
TAPE MOUNTED 22-16 F.E. TERMIN



TE Part #4-1971773-3
POWER TRIPLE LOCK STD TEMP
PLUG



TE Part #2040974-1
PLUG HSG, MINI VP 1.0MM W TO B
CONN.



TE Part #2321918-5
PLUG HOUSING SDL2.5
WATERPROOF 5PIN




TE Part #2321920-5
PERIMETER SEAL PLUG HOUSING
5PIN



TE Part #2321922-5
REAR WIRE SEAL 5PIN



TE Part #1742456-2
RT .265 DIA TERMINAL 10-6 AWG
TPCU



TE Part #3-644795-3
03P MTA100 CONN ASSY W/TBS LF

Documents

Product Drawings

[KNIFE DISCONNECT,BODY 22-16](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[35610](#)