



ALPHA TECHNICS 5000 SERIES PRECISION THERMOMETERS

Alpha Technics (now part of TE Connectivity) provides high accuracy Temperature Verification Kits and Thermometers used to ensure diagnostic and life science equipment and manufacturing operations are running at ideal temperatures for test accuracy and regulatory compliance.

The 5000 series thermometers offer the advantage of being a portable device with the accuracy of laboratory level equipment.

Benefits

- Large collection of standard probes
- Good long-term stability
- High Accuracy and Precision
- CE Marked
- RoHS Compliant
- ISO 17025 Calibration Available

Applications

- Calibration Laboratories
- Chemical and Medical Laboratories
- Universities/Research applications
- Industrial applications requiring high accuracy
- General Applications requiring high accuracy
- Data Logging applications

Specifications


Resolution	0.01°C
Measurement Uncertainty	± 0.05°C
Measurement Temperature Range	-20°C to 130°C
Display Units	°C or °F
Power	9V Battery (included)
Outputs	Virtual COM port over USB

5000 SERIES THERMOMETERS


Ordering Information

Description	Part Number
Thermometer only with ¼" Phone Plug Compatible with YSI 400 Series Probes	20018975-11
Thermometer with Tubular Probe (2.25"L, 0.156"OD), 7' Cable	20018975-20
Thermometer with Tubular Probe (4.85"L, 0.156"OD), 7' Cable	20018975-21
Thermometer with Tubular Probe (6.5"L, 0.156"OD), 7' Cable	20018975-22
Thermometer with Tubular Probe (12"L, 0.156"OD), 7' Cable	20018975-23
Thermometer with Needle Probe (1.5"L, 0.030"OD), 7' Cable	20018975-24
Thermometer with Needle Probe (0.70"L, 0.030"OD), 7' Cable	20018975-25

Product Family



Needle Probe



NORTH AMERICA
Tel +1 800 522 6752
customercare.alphatech@te.com

EUROPE
Tel +31 73 624 6999
customercare.alphatech@te.com

ASIA
Tel +86 0400 820 6015
customercare.alphatech@te.com

te.com/sensors

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Corporation. All Rights Reserved.

Version # 09/2021



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[20018975-22](#)