



HW

TE Internal #: D07339-000

Standard Labels, UL, Width 19.1 mm [.75 in], Height 6.4 mm [.25 in], White, Polyester, Label Thickness 97 Micron, HW

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > HW High Tack White Polyester Labels



Label Type: Industrial Label

Label Style: Die-Cut

Label Adhesive Type: High Tack Permanent Acrylic Adhesive

Compatible With Agency/Standards Products: UL

Product Width: 19.1 mm [.75 in]

[All HW High Tack White Polyester Labels \(46\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Polyester

Dimensions

Product Width	19.1 mm[.75 in]
Product Height	6.4 mm[.25 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	4
Label Style	Die-Cut
Length of Label Roll	23.75 m[77.91 ft]
Label Thickness	97 Micron

Industry Standards

Compatible With Agency/Standards Products	UL
---	----



Packaging Features

Packaging Quantity	10000
Packaging Method	Roll

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



Also in the Series

HW

Standard Labels(46)

Customers Also Bought

TE Part #5747840-4
HD-20 PLUG RA .318 FMS BD-LK 4

TE Part #2-5747707-0
15 RCPT SP/FMS BRDLK

TE Part #GA10K3A1A
DISCRETE 10K OHMS,+/-0.1C FROM
0C TO 70C

TE Part #650473-5
096 EURO TYPE C PIN ST ASSY

TE Part #1217151-1
187 FASTON,PIGGYBACK REC.,18-14
AWG,TPBR

TE Part #2-1393237-8
RT424012F

TE Part #1217084-1
FASTON 187 PIGGY-BACK REC 22-18
AWG TPBR

TE Part #2-350377-0
MR SPLT GROMET .156 DIA BLK LF

TE Part #1SNK900603R0000
JB85-3

TE Part #EC7548-000
HL104WE1NF033B

Documents

Product Drawings

HW-191064-10-9

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English



HW High Tack White Polyester labels

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HW-191064-10-9](#)