






- | | | | | | | | | |
|--|--|--|----------|--------------|--|--|-------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN
M. STORRY | 05-13-99 | |  Tyco Electronics Corporation
Harrisburg, PA 17105 | | | |
| | | CHK
E. PAULUS | 06-10-99 | | | | | |
| DIMENSIONS:
INCHES
 | | TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± —
1 PLC ± —
2 PLC ± .010
3 PLC ± .005
4 PLC ± — ± 1°
ANGLES | | APVD — | | NAME

PLUG ASSEMBLY, TWO ROW DUALOBE,
DUCKBILL LEADS,
PLASTIC OR METAL | | |
| | | PRODUCT SPEC
— | | | | | | |
| | | APPLICATION SPEC
— | | | | | | |
| MATERIAL


SEE NOTES | | FINISH

SEE NOTES | | WEIGHT
— | SIZE
A2 | CAGE CODE
00779 | DRAWING NO
C-1589066 | RESTRICTED TO
— |
| CUSTOMER DRAWING | | | | SCALE
8:1 | SHEET
1 | OF
2 | REV
D | |

LOC	DIST	REVISIONS				
DF	D0	P	LTR	DESCRIPTION	DATE	DWN APVD
		D		UPDATE PER 0H2Y-0164-04	05-12-04	JDM MKS



FLEX TOP VIEW
SIZE 15 SHOWN FOR REFERENCE



FLEX BOTTOM VIEW

TYPICAL FLEX PAD LAYOUT

SIZE	A DIM MAX	D DIM	E DIM
09	.150	.0500	.0375
15	.225	.0875	.0750
25	.350	.1500	.1375
37	.500	.2250	.2125
51	.675	.3125	.3000
65	.850	.4000	.3875

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .010
3 PLC ± .005
4 PLC ± -
ANGLES ± 1°
FINISH -

DWN M. STORRY 05-13-99
CHK E. PAULUS 06-10-99
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -
CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, PA 17105

NAME
PLUG ASSEMBLY, TWO ROW DUALOBE,
DUCKBILL LEADS,
PLASTIC OR METAL

SIZE A2
CAGE CODE 00779
DRAWING NO C=1589066
SCALE 8:1
SHEET 2 OF 2
REV D

RESTRICTED TO -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[STM02511378PCQ](#)