




- ① -A- SHALL BE THE INTERSECTION OF THE POST AND THE HOUSING
- ② ASSEMBLY TO BE CUT TO SIZE AS REQUIRED
- ③ ASSEMBLY MAY NOT EXCEED THE BOW LIMITATIONS AS STATED IN AMP TEST SPEC NO 102-25044
- ④ THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POSTS AND THE HOUSING
- ⑤ RETENTIVE POSTS PER 115-1166-1 FOR ACTIVE POSITION SIZES OF 6 AND BELOW. (SEE TABLE FOR LOCATIONS)
- ⑥ RETENTIVE POSTS PER 115-1133-5 FOR ACTIVE POSITION SIZES OF 7 AND ABOVE. (SEE TABLE FOR LOCATIONS)
- ⑦ $\Phi .020 \text{ } \textcircled{M}$ FOR KINKED TAILS
- ⑧ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		15,16	1,2	32	3-147550-7	104832-1	32	2-104352-1
		39,40	1,2	80	1-104818-4	104832-1	80	2-104352-0
		29,30	1,2	60	1-104818-4	104832-1	60	1-104352-9
		24,25	1,2	50	1-104818-4	104832-1	50	1-104352-8
		19,20	1,2	40	1-104818-4	104832-1	40	1-104352-7
		16,17	1,2	34	1-104818-4	104832-1	34	1-104352-6
		14,15	1,2	30	1-104818-4	104832-1	30	1-104352-5
		13,14	1,2	28	1-104818-4	104832-1	28	1-104352-4
		12,13	1,2	26	1-104818-4	104832-1	26	1-104352-3
		11,12	1,2	24	1-104818-4	104832-1	24	1-104352-2
		10,11	1,2	22	1-104818-4	104832-1	22	1-104352-1
		9,10	1,2	20	1-104818-4	104832-1	20	1-104352-0
		8,9	1,2	18	1-104818-4	104832-1	18	1-104352-9
		7,8	1,2	16	1-104818-4	104832-1	16	1-104352-8
		6,7	1,2	14	1-104818-4	104832-1	14	104352-7
		5,6	1,2	12	1-104818-4	104832-1	12	1-104352-6
		4,5	1,2	10	1-104818-4	104832-1	10	104352-5
		3,4	1,2	8	1-104818-4	104832-1	8	104352-4
		ALL	ALL	6	1-104818-4	104832-1	6	1-104352-3
		ALL	ALL	4	1-104818-4	104832-1	4	104352-2
		ALL	ALL	2	1-104818-4	104832-1	2	104352-1
	RETENTION FEATURE	ROW N	ROW M	QTY	PART NUMBER ②	HOUSING PART NO AS REQD ①	NO OF POSN	ASSEMBLY PART NUMBER
		HOLD-DOWN POST CONFIG LOCATIONS		BANDOLIER POST ASSEMBLY				

										DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK		2-8-88																							
										INCHES		0 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± .005 5 PLC ± -		R FEIDT		APVD		2-8-88		 Tyco Electronics Corporation Harrisburg, Pa																			
														R FEIDT																									
N1 REVISED PER ECO-09-020935										28AUG09		KK		AEG																									
N REV PER EC 0G3C-0495-03										09MAR04		MB		JG																									
P	LTR	REVISION RECORD				DATE		DWN		APVD				NAME		HEADER ASSY. MOD II, BREAKAWAY, DBL ROW, .100X100 VERT. .025 SO POSTS W/ HOLD- DOWN CONFIG																							
										ANGLES ±		-				SCALE		4:1		SIZE		A1		DRAWING NO		104352		SHEET		1		OF		1		REV		N1	
										SURFACE TEXTURE																													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-104352-0](#)