

- | | |
|---|---|
|  | TE LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION. |
|  | MARK PART NUMBER AND DATE CODE IN APPROXIMATE LOCATION SHOWN, EITHER END. |



101.60[4.000]	40		3-147733-9
99.06[3.900]	39		3-147733-8
96.52[3.800]	38		3-147733-7
93.98[3.700]	37		3-147733-6
91.44[3.600]	36		3-147733-5
88.90[3.500]	35		3-147733-4
86.36[3.400]	34		3-147733-3
83.82[3.300]	33		3-147733-2
81.28[3.200]	32		3-147733-1
78.74[3.100]	31		3-147733-0
76.20[3.000]	30		2-147733-9
73.66[2.900]	29		2-147733-8
71.12[2.800]	28		2-147733-7
68.58[2.700]	27		2-147733-6
66.04[2.600]	26		2-147733-5
63.50[2.500]	25		2-147733-4
60.96[2.400]	24		2-147733-3
58.42[2.300]	23		2-147733-2
55.88[2.200]	22		2-147733-1
53.34[2.100]	21		2-147733-0
50.80[2.000]	20		1-147733-9
48.26[1.900]	19		1-147733-8
45.72[1.800]	18		1-147733-7
43.18[1.700]	17		1-147733-6
40.64[1.600]	16		1-147733-5
38.10[1.500]	15		1-147733-4
35.56[1.400]	14		1-147733-3
33.02[1.300]	13		1-147733-2
30.48[1.200]	12		1-147733-1
27.94[1.100]	11		1-147733-0
25.40[1.000]	10		147733-9
22.86[.900]	9		147733-8
20.32[.800]	8		147733-7
17.78[.700]	7		147733-6
15.24[.600]	6		147733-5
12.70[.500]	5	8	147733-4 7
10.16[.400]	4		147733-3 8
7.62[.300]	3	8	147733-2
5.08[.200]	2		147733-1 8

A		NO OF POSN		PART NUMBER		A		NO OF POSN		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN M.BINNER		250CT01		 TE Connectivity	
						CHK —		—			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		APVD —		NAME AMPMODU MODII RECPT. ASSY., HORZ., SURFACE MOUNT, .100CL, 1 ROW CLOSED ENTRY, END STACK					
				PRODUCT SPEC —							
MATERIAL 1 2				APPLICATION SPEC —							
				—							
				SIZE A2							
FINISH 3		WEIGHT —		CAGE CODE 00779		DRAWING NO C=147733		RESTRICTED TO —			
CUSTOMER DRAWING						SCALE 5:1		SHEET 1 of 1		REV F4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[147733-5](#)