

SPECIAL

APPLICATOR PARTS LIST				TYPE ENDFEED 30° ROTATED THRU SPLKE			AMP INCORPORATED HARRISBURG, PENNA.				
NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA			TERMINALS
1	WIRE CRIMPER	1	463340-1	42				TO APPLY TERMINAL			40509
2	INS. CRIMPER			43	SPRING SLIDE 3/4" D	1	2-24017-7	WIRE SIZE			
3	ANVIL	1	463329-1	44	FEED PLATE RETAINER	1	372998	CRIMP HEIGHT			
4	ANVIL SPACER			45				051+16 .089			
5	SHEAR BLADE	1	463326-1	46				051+14 .097			
6	PLATE-FEED	1	463327-1	47							
7	SHEAR BLADE SPACER			48							
8	FRONT SHEAR PLATE			49							
9	REAR ANVIL SPACER PLT.			50				CRIMP	SIZE	TYPE	FEED
10	FRONT ANVIL SPACER PLT.			51				WIRE	140	F	
11	TOOL SPACER			52				INSUL.			.217
12	CRIMP SPACER			53				SLEEVED			
13	FRONT STRIP GUIDE			54				INSULATION RANGE	WIRE RANGE CMA		
14	REAR STRIP GUIDE			55	SG, HD. SET SCR.	1	21077-7	3200-8200			
15	RAM	1	471167	56	NUT, JAM	1	22202-1	EXPLODED VIEW			
16	TOOL HOLDER	1	465401-1	57				A-6010-17			
17	ADJ. CRIMP MOUNT			58				REMARKS:			
18	ADJ. BLOCK			59							
19	APPLICATOR MOUNT ASSY.	1	473933-8	60							
20	BASE PLATE			61							
21	BASE BLOCK			62							
22	STRIP GUIDE PLATE			63							
23	ANVIL HOLDER	1	374348	64	AIR FEED ASSY	1	690021-1				
24	AUX. ANVIL HOLDER			65	TENSION ADJ. PLATE	1	374999				
25	STRIPPER	1	376945	MISCELLANEOUS							
26	STRIPPER MOUNT			66	LUBRICATOR ASSY.	1	464518-1				
27	RETAINER PLATE			67	TERMINAL LUB.	REF	252931-2				
28	STRIPPER MOUNT BRACKET			68							
29	STRIPPER BUSHING			69	BLOCK-REEL BRKT. MT. 30	1	453602-1				
30	STOCK DRAG	1	372990	70							
31	STOCK DRAG NUT	1	21022-4	71							
32	STOCK DRAG STUD	1	21015-8	72							
33	STOCK DRAG SPRING	1	373469	REV. REVISION RECORD				DATE	BY	ECN	
34	STOCK DRAG ADJ. SCREW	2	372997	A	36 WAS 811432-1	840C33	8/30/76	LA			
35	FEED FINGER HOLDER			A1	INACT. FRD		8/16/77	US	2161		
36	FEED FINGER	1	452817-1	B	ITEM 66 WAS -1		10/28/76	SB	2251		
37	FEED FINGER TIP			C	ITEM 66 WAS 465184-2		2/24/80	SG	2343		
38	FEED FINGER SPACER			D	EC-A-2724 90		4-3	BU			
39	BASE CASTING	1	570238								
40	GUARD	1	460582-6								
41											

**— INACTIVE —**

**FOR REPLACEMENT ONLY**

☐ DENOTES WEARING PARTS  
RECOMMEND PURCHASE REPLACEMENT

THIS APPLICATOR IS TO BE USED ON  
AMP-O-ELECTRIC 1-471273-2  
AMP-O-ELECTRIC AIR FEED

SERIAL NO. \_\_\_\_\_ DATE SHIPPED \_\_\_\_\_

CUSTOMER NAME AND ADDRESS \_\_\_\_\_

APPLICATOR NUMBER \_\_\_\_\_ REV. **D** **566239-1**

SHEET 1 of 1

FOR HARDWARE  
SEE 1-607526-7

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566239-1](#)