



REV	6162-217-1277
N/C	THRU 6162-224-1277

											TOOL INFORMATION		
DEUTSCH PART NUMBER	CONTACT TYPE	BIN CODE	COLOR BANDS			OUTER A Ø MAX	CONTACT B Ø MIN	INNER CONTACT C Ø MIN	CRIMP D Ø MAX	SLEEVE E Ø MIN	INNER CONTACT CRIMPING TOOL	CRIMP SLEEVE CRIMPING TOOL	INSERTION/ EXTRACTION
6162-217-1277	S	416	YELLOW	BROWN	BLUE	.110	.090	.0225	.169	.127	M22520/2-01 WITH M22520/2-34 POSITIONER	M22520/31-01 WITH M22520/31-02 POSITIONER	M81969/14-04
6162-218-1277	S	417	YELLOW	BROWN	VIOLET	.127	.108	.0225	.169	.144			
6162-219-1277	S	418	YELLOW	BROWN	GRAY	.127	.108	.0355	.169	.144			
6162-220-1277	S	419	YELLOW	BROWN	WHITE	.110	.090	.0355	.169	.127			
6162-221-1277	S	420	YELLOW	RED	BLACK	.110	.090	.0225	.169	.127			
6162-222-1277	S	421	YELLOW	RED	BROWN	.136	.117	.0270	.174	.156			
6162-223-1277	S	422	YELLOW	RED	RED	.110	.090	.0225	.169	.144			
6162-224-1277	S	423	YELLOW	RED	ORANGE	.127	.108	.0355	.174	.156			

6. THIS SHIELDED CONTACT WILL MEET ALL CABLE SIZES IN MIL-C-39029/75 AND/28. FOR CABLE SIZES REFER TO MIL-C-39029/75 AND /28.
5. CONTACTS PLATED .000050 MIN. GOLD PER MIL-G-45204.
4. ALL COMPONENTS MADE OF HIGH GRADE COPPER ALLOY. DIELECTRICS MADE FROM TEFLON.
3. DESIGNATED PARTS ARE SHIPPED LOOSE.
2. CONSULT FACTORY FOR AVAILABILITY.
1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

OTE:

SIGNATURE & DATE		CONTACT, SOCKET SIZE 12 SHIELDED MIL-C-39029/75 ENVELOPE	CP	MATL CODE
DR			The Deutsch Company ELECTRONIC COMPONENTS DIVISION Municipal Airport Banning, California	
CHK				
PE				
APPD				
SCALE	NONE	WT	C	6162-217-1277 THRU 6162-224-1277 CODE 11139 SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6162-218-1277](#)