




99M0111-16-9 Product Details

[Share](#) [Print](#) [Email](#)


99M0111-16-9

TE Internal Number: 0281513001

Active

Spec 99 and Spec 100 Wire and Cable

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 99M
- Cable Style = Primary
- Wire Size (AWG or Metric) = 16 AWG [1.23mm²]
- Number of Conductors = 1
- Equipment Wire Application

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Product Drawings: • Customer Drawing (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Related Products: • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Cable Type = Spec 99M • Cable Style = Primary Electrical Characteristics: • Wire Size (AWG or Metric) = 16 AWG [1.23mm²] • Voltage Rating (VAC) = 600 Dimensions: • Conductor Outer Diameter (mm [in]) = 1.42 [0.056] Body Features: • Wire Color = White • Nominal Outside Diameter (mm [in]) = 1.80 [0.071] • Wire Diameter (mm [in]) = 1.80 [0.071] • Conductor Type = Tin-Plated Copper Configuration Features: • Number of Conductors = 1	Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: • Wire Size - Details = 16 AWG 1.23 mm², 0.002 in², 19 x 29 AWG • Temperature Range (°C) = -55 - +125 Operation/Application: • Application = Equipment Wire Packaging Features: • Wire Source = United Kingdom Other: • Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[99M0111-16-9](#)