

44A0111-22-92-US Product Details


[Share](#)

[Print](#)

[Email](#)


44A0111-22-92-US

TE Internal Number: 282625-002

 **Active**

Spec 44, Spec 55 and Spec RCW Wire and Cable



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [WIRE, ELECTRIC, RADIATION-CROSSLINKED, TIN-COATED CO...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Cable Type](#) = Spec 44
- [Cable Style](#) = Primary

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Dimensions:

- Conductor Outer Diameter (mm [in]) = 0.79 [0.031]

Body Features:

- Wire Size (AWG/CM) = 22 AWG
- Conductor Type = Tin-Plated Copper
- Wire Color = White w/ Red Stripe
- Nominal Outside Diameter (mm [in]) = 1.19 [0.047]
- Wire Diameter (mm [in]) = 1.19 [0.047]

Configuration Features:

- Number of Conductors = 1

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Range (°C) = -65 - +150
- Wire Size - Details = 22 AWG 0.38 mm², 0.00059 in², 19 x 34 AWG

Operation/Application:

- Application = General Purpose - Lightweight

Packaging Features:

- Wire Source = United States

Other:

- Brand = Raychem

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[44A0111-22-92-US](#)