












LOC		DIST		REVISIONS				
-	-	-	LTR	DESCRIPTION	DATE	DWN	APVD	
		-	SEE SHEET 1			-	-	-







1*2 POSITIONS

1*3 POSITIONS

1*4 POSITIONS

1*5 POSITIONS



KEYING FOR 1*2 POS.

KEYING FOR 1*3 POS.

KEYING FOR 1*4 POS.

KEYING FOR 1*5 POS.

1*3	LEVEL 1	KEY A	1-1971772-3
		KEY B	2-1971772-3
		KEY C	3-1971772-3
		KEY D	4-1971772-3
	LEVEL 2	KEY A	5-1971772-3
		KEY B	6-1971772-3
		KEY C	7-1971772-3
		KEY D	8-1971772-3
1*2	LEVEL 1	KEY A	1-1971772-2
		KEY B	2-1971772-2
		KEY C	3-1971772-2
		KEY D	4-1971772-2
	LEVEL 2	KEY A	5-1971772-2
		KEY B	6-1971772-2
		KEY C	7-1971772-2
		KEY D	8-1971772-2
POS.	MATERIAL	KEY	P/N

1*4	LEVEL 1	KEY A	1-1971772-4
		KEY B	2-1971772-4
		KEY C	3-1971772-4
		KEY D	4-1971772-4
	LEVEL 2	KEY A	5-1971772-4
		KEY B	6-1971772-4
		KEY C	7-1971772-4
		KEY D	8-1971772-4
1*5	LEVEL 1	KEY A	1-1971772-7
		KEY B	2-1971772-7
		KEY C	3-1971772-7
		KEY D	4-1971772-7
	LEVEL 2	KEY A	5-1971772-7
		KEY B	6-1971772-7
		KEY C	7-1971772-7
		KEY D	8-1971772-7
POS.	MATERIAL	KEY	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN TOMMY.WU 06JUL2012
CHK HAPYE.WU 06JUL2012
APVD YUZHONG.MAO 06JUL2012

DIMENSIONS:

mm

0 PLC ±.35
1 PLC ±0.25
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±.
FINISH -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC 108-106118
APPLICATION SPEC 114-106118
WEIGHT -

MATERIAL

Customer Drawing

TE Connectivity

NAME CAP HOUSING,PANEL MOUNT,SINGLE ROW POWER TRIPLE LOCK

SIZE A100779C=1971772

RESTRICTED TO -

SCALE -

SHEET 2 OF 2

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1971772-4](#)