



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
010	RELEASED	7/21/95	S. Morley
011	REVISED PER ECN 95-0547	12/7/95	S. Morley
012	REVISED PER ECN 99-0001	DM 5/20/99	S. Morley
013	REVISED PER ECN 99-0001	DM 6/25/99	PCV 6/25/99

NOTES:

1. CONNECTOR CENTERLINES SHALL BE ALIGNED AS SHOWN WITHIN  $\pm 30^\circ$  FOR LENGTHS 165 MILLIMETERS OR LESS. LENGTHS ABOVE 165 MILLIMETERS SHALL HAVE CONNECTOR CENTERLINES ALIGNED AT RANDOM.

XX.X = mm  
.XXX = in

ELECTRICAL

Frequency	DC - 6 GHz
Nominal Impedance	50 ohms
Voltage Rating	250 Volts (VRMS Max.) @ Sea Level
VSWR	1.20:1 Max. @ 2GHz 1.40:1 Max. @ 6GHz
Insulation Resistance	1,000 Megohms Minimum @ 250VDC
Dielectric Withstanding Voltage	500 Volts (VRMS Minimum) @ Sea Level

MECHANICAL

Connector Durability	100 mating cycles
----------------------	-------------------

ENVIRONMENTAL

Temperature Rating	-40°C (-40°F) To +125°C (257°F)
--------------------	---------------------------------

CONNECTOR:

INNER & OUTER CONTACTS

BERYLLIUM COPPER ALLOY CDA172

GOLD PLATE OVER NICKEL PLATE

DIELECTRIC

POLYPROPYLENE, GF

N/A

CABLE:

JACKET

FEP FLUOROCARBON PER ASTM-D2116

N/A

SHIELD

COPPER WIRE, 44AWG

SILVER PLATED

DIELECTRIC

PTFE FLUOROCARBON PER ASTM-D1457

N/A

CENTER CONDUCTOR

COPPER CLAD STEEL, 30AWG

SILVER PLATED

COMPONENT

MATERIAL

FINISH

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN MILLIMETERS  
TOLERANCE ON  
FRAC DEC ANGLES  
- - -

DRAWN BY  
P. RESNICK DATE  
3 JUNE 94

CHECKED BY

APPD BY

AMP Incorporated

140 Fourth Avenue  
Waltham, MA 02451-7599

AMP

These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.

USE ASSY PROCEDURE

NO. A.P. N/A

TITLE

SSMT RIGHT ANGLE JACK  
TO JACK CABLE ASSEMBLY

SIZE

B

CODE IDENT NO.

26805

9960-1050-24

REV

013

SCALE 10:1

CABLE

TYPE

SSMT-FLEX

SHEET 1 OF 1

CUSTOMER DRAWING

AMP PART # 1064522-1  
SHEET 1 OF 1 REV A

OUTLINE, -50 AND B/M MUST CARRY  
THE SAME MAJOR REVISION LEVEL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9960-1050-24](#)