




Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)

204978-3 Product Details

[Share](#)[Print](#)[Email](#)

204978-3
(M39029/11-146)
TE Internal Number: 204978-3

Active

[View 3D PDF](#)

ARINC 600/404 Contacts and Accessories



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact
- Contact Type = Pin
- Gold Contact Plating, Mating Area, Material
- Contact Size = 16
- Length = 25.58 mm

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [PIN CONTACT, SIZE 16, ARINC 600 \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [AMP* ARINC 404 RACK-AND-PANEL CONNECTORS SERIES R, R... \(PDF, English\)](#)
- [Application Tooling for Screw-Machine Contacts \(PDF, English\)](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version P\)](#)
- [3D Model \(IGES, Version P\)](#)
- [3D Model \(STEP, Version P\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Color Code](#) = Brown/Yellow/Blue
- [Connector Family](#) = ARINC 404

Dimensions:

- [Length \(mm \[in\]\)](#) = 25.58 [1.007]

Body Features:

- [Material](#) = Copper Alloy

Contact Features:

- [Contact Type](#) = Pin
- [Contact Plating, Mating Area, Material](#) = Gold
- [Contact Size](#) = 16
- [Contact Configuration](#) = Type XVII

Industry Standards:

- [Government/Industry Qualification](#) = Yes
- [Government/Industry Part Number](#) = M39029/11-146
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Other:

- [Brand](#) = AMP

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Supplier Portal](#)

[Product Compliance Support Center](#)

[Manage Your Account](#)

[Careers](#)

[Site Map](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Keep Me Informed



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39029/11-146](#)