

THIS IS A CONTROLLED DOCUMENT.

AMP 1281 (7/63)

APPLICATOR PARTS LIST

TYPE

LENGTHWISE BRUSH CONT.
AMPLIVARMAGNET PICK UP AMP INCORPORATED LEFT
WIRE STOP HARRISBURG, PENNA. HAND

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA				TERMINALS
1	■ WIRE CRIMPER	1	453917-3	42				CMA	CRIMP HT			62214-1
2	■ INS. CRIMPER			43				700	.057			
3	■ ANVIL	1	1-4734050	44	HOLD DOWN	1	375826	800	.058			
4	ANVIL SPACER			45				1000	.060			
5	■ SHEAR BLADE	1	457819-2	46				1200	.061			
6	■ REAR SHEAR PLATE	1	385013-4	47				1400	.063			
7	SHEAR BLADE SPACER	2	370954	48				1600	.063			
8	■ FRONT SHEAR PLATE	1	372064	49				1800	.064			
9	REAR ANVIL SPACER PLT.			50				2000	.066			
10	FRONT ANVIL SPACER PLT.			51				CRIMP	SIZE	TYPE	FEED	
11	TOOL SPACER	1	370439	52				WIRE	.090	F		
12	CRIMP SPACER			53	HOLD DOWN	1	1-811227-1	INSUL.			.500	
13	FRONT STRIP GUIDE	1	371638	54				SLEEVED				
14	REAR STRIP GUIDE	1	379034-2	55				INSULATION RANGE	WIRE RANGE MAG			
15	RAM	1	471911	56	FLOATING WIRE STOP	1	565081-2					
16	TOOL HOLDER			57	BUSHING	REF	811258-2	EXPLODED VIEW				
17	ADJ. CRIMP MOUNT			58	STOP	REF	811259-2	A-6000 A-6000-1				
18	ADJ. BLOCK			59	SPACER	REF	811260-1	REMARKS: ▲ INDICATES				
19	APPLICATOR MOUNT	1	570656	60	SLIDE	REF	811280-1	PARTS USED ON				
20	BASE PLATE			61	MOUNT	REF	811282-1	565081-2 ASS'Y				
21	BASE BLOCK			62				(ITEM 56)				
22	STRIP GUIDE PLATE			63	HOLDER-MAGNET	REF	811284-1					
23	ANVIL HOLDER	1	370526	64	BRACKET	REF	811285-1					
24	AUX. ANVIL HOLDER	1	377515	65								
25	STRIPPER				MISCELLANEOUS							
26	STRIPPER MOUNT	▲ REF	811323-1	66	MAGNET	REF	811287-1	■ DENOTES WEARING PARTS				
27	RETAINER PLATE	▲ REF	372251	67	WIRE STOP	REF	465344-2	RECOMMEND PURCHASE REPLACEMENT				
28	STRIPPER MOUNT BRACKET			68								
29	STRIPPER BUSHING			69								
30	STOCK DRAG	1	375381	70								
31	STOCK DRAG HANDLE			71	TENSION ADJ PLATE	1	374999					
32	STOCK DRAG STUD	2	354045-1	72								
33	STOCK DRAG SPRING	2	1-23847-1	REV.	REVISION RECORD	DATE	BY	ECN				
34	STOCK DRAG ADJ. SCREW	2	372997	03	REINSTATE R-7462	9/20/87	PM	—				
35	FEED FINGER HOLDER			A	ECN A-395892	9-92	MD	—				
36	FEED FINGER	1	375093	A1	ECN 0150-0249-03	3-03	WY	—				
37	FEED FINGER TIP											
38	FEED FINGER SPACER											
39	BASE CASTING	1	570238									
40	GUARD ASS'Y.	1	457664-2									
41												

APPLICATOR NUMBER	REV.	566149-1	SHEET	1 OF 1
-------------------	------	----------	-------	--------

CASE CODE
00778

CUSTOMER AND ASSEMBLY DRAWING

RESTRICTED TO

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566149-1](#)