

CUSTOMER DRAWING
UNPUBLISHED

USED ON 603995

603997

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO
YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE
BY YOU TO OTHERS WITHOUT WRITTEN AUTHORIZATION
FROM AMP SPECIAL INDUSTRIES, VALLEY FORGE, PA., U. S. A.

DO NOT SCALE DRAWING

603997-1 V-BLOCK FOR CABLE, DIAMETER
RANGE, 3.5 - 5 mm (.14" - .20")
(COLOR RED)
VENDOR P/N "VR"

603997-2 V-BLOCK FOR CABLE, DIAMETER
RANGE, 5 - 6.4 mm (.20" - .25")
(COLOR BLUE)
VENDOR P/N "VB"

603997-3 V-BLOCK FOR CABLE, DIAMETER
RANGE, 6.4 - 7.6 mm (.25" - .30")
(COLOR YELLOW)
VENDOR P/N "VY"

603997-4 V-BLOCK FOR CABLE, DIAMETER
RANGE 2.5 - 3.1 mm (.10" - .12")
(COLOR WHITE)
VENDOR P/N "VW"

NOTE: INSPECT FOR COLOR, DIMENSIONS NOT REQUIRED

DWG SIZE		PART NO		DESCRIPTION		ITEM NO
← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)						
QTY REQD PER ASSY		PARTS LIST				
				MATERIAL H	HEAT TREAT H	FINISH H
				DIMENSIONS IN INCHES. TOLERANCES UNLESS OTHERWISE SPECIFIED: 2 PL DEC ± .005 3 PL DEC ± .005 4 PL DEC ± .005 ANGLES ± .005 SURF TEXTURE: ✓ REMOVE BURRS, BREAK SHARP EDGES .015R MAX		
				DR ME 6/2/77 CHK J. Detrick 7/16/77 REL J. Hamed 7-90 AMP SPECIAL INDUSTRIES Division of AMP Products Corporation Valley Forge, Pa. 19402 A Subsidiary of AMP Incorporated		
				NAME V-BLOCK, CABLE		
A	EN 071990 NO-4	RJ	7-90	SCALE NTS		
O	RELEASED	RJ	7-90	DWG NO 603997		
P	F	LTR	REVISION RECORD	APP	DATE	SHEET A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[603997-3](#)