




4

3

2

1

CONVERSION CHART	
INCH	MM
.010	0.25
.146	3.71
.257	6.53
.350	8.89
.385	9.78
.421	10.69
.590	15.00
.591	15.01
.827	21.00

64S64T64E**NOTES:**


1. INTERPRET DRAWING PER ASME Y14.5M-1994.
2. LENS BUTTON SET INCLUDES:  
(\*) PLASTIC DEFUSER BUTTON  
CLEAR PLASTIC COVER.
3. FITS BOTH OILTIGHT AND NON-OILTIGHT MODELS.
4. (\*) SPECIFY COLOR: (2) = RED  
(3) = ORANGE  
(4) = YELLOW  
(5) = GREEN  
(6) = BLUE  
(9) = WHITE/CLEAR

**OUTLINE DRAWING**

SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE

THIS IS A C.A.D. GENERATED DRAWING.  
DO NOT MAKE MANUAL REVISIONS TO MASTER.

REV	A	B	3
REVISIONS	INITIAL RELEASE ESR/DS06 PS 12-8-87 APP'D: SMM 12-8-87	REVISED ECO/3147 T.H. 3-1-89 APP'D: C.F. 3-1-89	REVISED ECO/392-95 S.KIRCORTAN 6-14-95 APP'D: MLL 6/2/95

THIRD ANGLE  
PROJECTION

TOLERANCES (EXCEPT AS NOTED)  
ANGULAR = ±1°  
DECIMAL .XX = ±  
DECIMAL .XXX = ±.010  
DECIMAL .XXXX = ±

AUGAT CONFIDENTIAL  
This document contains information  
which is the exclusive property of  
Augat Inc.  
Distribution, reproduction or use by  
others is not permitted without the  
expressed written consent of Augat  
Inc.

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
DO NOT SCALE PRINT

FILE NAME: 80811OUT  
DIRECTORY: PSHSWCH

MATERIAL:  
SEE SPECIFICATIONS

FINISH:  
SEE SPECIFICATIONS

ORIGINAL DATE  
OF DRAWING: 12-9-87

DRAWN: L.M.  
DATE: 3-1-89

CHECKED: P.S.  
DATE: 12-9-87

APPROVED: S.M.M.  
DATE: 12-9-87

CODE IDENT. NO. 91506  
DWG. SIZE C

NEXT ASSY:

**AUGAT** INC.  
452 JOHN DIETSCH BLVD.  
ATTLEBORO FALLS, MASS. 02763

TITLE: **OUTLINE DRAWING**  
LENS SET  
64\*-\* SERIES

DWG. NO. 80811  
REV. 3

PRODUCT CODE:  
SCALE: SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[64T4](#)