




4

3

2

1

CONVERSION CHART	
INCH	MM
.010	0.25
.146	3.71
.257	6.53
.350	8.89
.385	9.78
.421	10.69
.590	15.00
.591	15.01
.827	21.00

64S64T64E**NOTES:**

1. INTERPRET DRAWING PER ASME Y14.5M-1994.
2. LENS BUTTON SET INCLUDES:
(*) PLASTIC DEFUSER BUTTON
CLEAR PLASTIC COVER.
3. FITS BOTH OILTIGHT AND NON-OILTIGHT MODELS.
4. (*) SPECIFY COLOR: (2) = RED
(3) = ORANGE
(4) = YELLOW
(5) = GREEN
(6) = BLUE
(9) = WHITE/CLEAR

**OUTLINE DRAWING**

SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE

THIS IS A C.A.D. GENERATED DRAWING.
DO NOT MAKE MANUAL REVISIONS TO MASTER.

REV	A	B	3
REVISIONS	INITIAL RELEASE ESR/DS06 PS 12-8-87 APP'D: SMM 12-8-87	REVISED ECO/3147 T.H. 3-1-89 APP'D: C.F. 3-1-89	REVISED ECO/392-95 S.KIRCORTAN 6-14-95 APP'D: MLL 6/2/95

THIRD ANGLE
PROJECTIONTOLERANCES (EXCEPT AS NOTED)
ANGULAR = ±1°
DECIMAL .XX = ±
DECIMAL .XXX = ±.010
DECIMAL .XXXX = ±AUGAT CONFIDENTIAL
This document contains information
which is the exclusive property of
Augat Inc.
Distribution, reproduction or use by
others is not permitted without the
expressed written consent of Augat
Inc.UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
DO NOT SCALE PRINTFILE NAME: 80811OUT
DIRECTORY: PSHSWCHMATERIAL:
SEE SPECIFICATIONSFINISH:
SEE SPECIFICATIONSORIGINAL DATE
OF DRAWING: 12-9-87DRAWN: L.M.
DATE: 3-1-89CHECKED: P.S.
DATE: 12-9-87APPROVED: S.M.M.
DATE: 12-9-87CODE IDENT. NO. 91506
DWG. SIZE C

NEXT ASSY:

AUGAT INC.
452 JOHN DIETSCH BLVD.
ATTLEBORO FALLS, MASS. 02763TITLE: **OUTLINE DRAWING**
LENS SET
64*-* SERIESDWG. NO. 80811
REV. 3PRODUCT CODE:
SCALE: SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[64S5](#)