



TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**



Product Drawings

TE CONNECTIVITY (TE)
PLG ASSY,25 POS,AMPLIMITE
[AMPLIMITE](#) | [AMPLIMITE](#)

206800-1
TE Internal Number: 206800-1
Mil-Spec: 311P409-3P-B-15

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Connector Style **Plug**

Number of Positions **25**

Power/Signal/Coax Combination **No**

Shell Size **3**

Contact Style **Crimp Snap-In**

[AMPLIMITE NONMAGNETIC PLUG ASSEMBLY WITHOUT SIZE 20 PIN
CONTACTS, SERIES 109, SHELL SIZE 3, 25 POSITION](#)

PDF
English



Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style	Plug
Shell Size	3
Connector & Contact Terminates To	Wire & Cable
Blindmate	No
Product Type	Connector

Configuration Features

Number of Positions	25
Power/Signal/Coax Combination	No

Body Features

Non-Magnetic	Yes
Shell Material	Brass
Shell Plating Material	Gold
Retention Clip Material	Copper Alloy

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English

3D PDF


PDF
English



Contact Features	Contact Style	Crimp Snap-In
	Contact Size	20
	Contact Mating Area Plating Thickness (µin)	100 – 150
	Contact Type	Pin
	Contact Mating Area Plating Material	Gold
	Contact Base Material	Copper
Mechanical Attachment	Mounting Hole Diameter	3.91 mm [.154 in]
Operation/Application	ULTRA-LITE Connector	No
Packaging Features	Packaging Method	Package
Statement of Compliance	Statement of Compliance PDF	

Compatible Products [> Contact Product Support](#)

Also in the Series | [AMPLIMITE](#)





Customers Also Bought

CIRCUIT BREAKERS	BOX MOUNT D-SUB CONNECTORS	BOX MOUNT D-SUB CONNECTORS	BOX MOUNT D-SUB CONNECTORS
			
W68-X2Q12-7=M6/M7/M9/W6/W7 W68-X2Q12-7	AMPLIMITE RECEPT ASY, 25 POS 206801-1	PLUG ASSY, 15 POSN, AMPLMTE 206798-1	PLUG ASSY, 37 POSN, AMPLIMITE 206802-1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[311P409-3P-B-15](#)