



T-1 Sub-Midget Flange Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM7234	5.0	.030	.030	16,000	C-2F
CM7235	5.0	.080	.150	3,000	C-2R
CM7236	5.0	.115	.200	5,000	C-2R
CM7237	5.0	.120	.200	5,000	C-2R
CM7238	5.0	.115	.100	10,000	C-2R
CM7239	5.0	.125	.250	5,000	C-2R
CM7250	5.0	.045	.040	10,000	C-2R
CM8022	5.0	.020	.030	10,000	C-2R
CM8605	5.0	.017	.005	10,000	C-2R
CM7240	10.0	.027	.100	10,000	C-2F
CM32	12.0	.060	.130	16,000	C-2F
CM22	14.0	.040	.130	10,000	C-2V
CM8112	14.0	.065	.150	10,000	C-2F
CM7241	18.0	.026	.150	10,000	C-2F
CM6839	28.0	.024	.130	4,000	CC-2F

T-1 Bi-Pin Base (.050")



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM7252	1.25	.012	.004	1,000	C-6
CM7253	1.35	.220	.020	25,000	C-2R
CM7254	1.5	.015	.010	5,000	C-2R
CM7255	1.5	.075	.030	16,000	C-2R
CM7256	2.5	.015	.001	10,000	C-2R
CM7257	2.5	.320	.210	5,000	C-2R
CM7732	2.5	.100	.100	10,000	C-2R
CM3229	3.0	.015	.020	5,000	C-6
CM7258	3.0	.008	.001	16,000	C-2R
CM7259	3.0	.013	.001	16,000	C-2R
CM7260	3.0	.060	.030	100,000	C-2R
CM7261	3.0	.120	.150	16,000	C-2R
CM7022	5.0	.020	.030	10,000	C-2R
CM7262	5.0	.017	.005	10,000	C-2R
CM7263	5.0	.030	.030	16,000	C-2R
CM7264	5.0	.045	.040	10,000	C-2R
CM7265	5.0	.060	.150	5,000	C-2R
CM7266	5.0	.080	.150	15,000	C-2R
CM7267	5.0	.115	.200	5,000	C-2R
CM7268	5.0	.125	.250	5,000	C-2R
CM7270	5.0	.060	.030	60,000	C-2R
CM7271	5.0	.060	.050	40,000	C-2R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

7241 7022