


VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: FOLD & TIE



CONNECTOR TYPE:  
IEC 60320 C-13

- NOTES**
- 1) CORDAGE: HD5VV-F 3x1.0MM<sup>2</sup>, GRAY-RAL#7032
  - 2) APPROVALS:
  - 3) RATING: 10 AMP @ 250 VOLTS
  - 4) PACKAGING: 25 PIECES PER CARTON
  - 5) ALL DIMENSIONS IN MILLIMETERS

|          |  |  |  |  |  |   |  |  |  |   |  |  |  |                  |  |
|----------|--|--|--|--|--|---|--|--|--|---|--|--|--|------------------|--|
|          |  | <input checked="" type="checkbox"/> Indianapolis, IN<br><input type="checkbox"/> Conover, N.C.<br><input type="checkbox"/> Freemont, CA<br><input type="checkbox"/> Aguascalientes, MX<br><input type="checkbox"/> Tijuana, Mexico<br><input type="checkbox"/> Hermosillo, MX<br><input type="checkbox"/> Clinton, AR<br><input type="checkbox"/> Kanata, Canada |  | <b>Proprietary Notice:</b><br>This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc. |  | <b>MATERIAL:</b><br>PLUG, PVC, GRAY-RAL#7032<br>CONNECTOR, PVC, GRAY-RAL#7032<br>JACKET, PVC, GRAY-RAL#7032<br>LEAD FREE & ROHS COMPLIANT |  | <b>FINISH:</b><br>JACKET, SMOOTH   |  | <b>SCALE:</b><br>NDT TO SCALE<br>ECD: N/A |  | <b>ITEM DESCRIPTION</b><br>EUROPEAN POWER CORD<br>2 METERS |  |                  |  |
| <b>1</b> |  | C.U.D - NEW RELEASE  |  | 9/25/07  |  | SCALE: N/A  |  | TOLERANCE SPECIFIED<br>.XXX ± .005<br>.XX ± .02<br>.X ± .03<br>FRACT. ± 1/32<br>ANGULAR ± 1/2° |  | APPROVED<br>STC                           |  | DRAWN BY<br>STC  |  | DATE:<br>9/25/07 |  |
| PART NO. |  | 17820 326 H25  |  |  |  |   |  |  |  |   |  |  |  |                  |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Volex:

17820 326 H25