



Front panels



As filler panel, flat

Material:
2.5 mm aluminum, natural-anodized.



! Also required:

Collar screws and plastic collars,
packs of 100 sets, order no. 3658.160,
see page 164

HP	a mm	W (B) mm	b mm	Order No.						
				1 U H = 39.8	2 U H = 84.25	3 U H = 128.7	4 U H = 173.15	6 U H = 262.05	7 U H = 306.5	9 U H = 395.4
2	9.8	—	—	—	—	3684.889	—	3684.911	—	3684.738
3	14.9	—	—	—	—	3684.890	—	3684.912	—	—
4	20.0	—	—	—	—	3684.891	—	3684.913	—	3684.739
5	25.1	—	—	—	—	3684.892	—	3684.914	—	—
6	30.1	—	—	—	—	3684.893	—	3684.915	—	—
7	35.2	—	—	—	—	3684.894	—	3684.916	—	—
8	40.3	—	—	—	—	3684.895	—	3684.917	—	3684.740
10	50.5	35.6	—	—	—	3684.896	—	3684.918	—	—
12	60.6	45.7	—	—	—	3684.897	—	3684.919	—	3684.741
14	70.8	55.9	—	—	—	3684.898	—	3684.920	—	—
20	101.3	86.4	—	—	—	3684.899	—	3684.921	—	—
21	106.4	91.4	—	—	3685.350	3684.900	—	3684.922	—	—
24	121.7	106.7	—	—	3685.429	—	—	—	—	—
27	136.8	121.9	—	—	—	3684.901	—	3684.923	—	—
28	141.9	127.0	—	—	—	3684.902	—	3684.924	—	—
40	202.9	188.0	—	—	—	3684.903	—	3684.976	—	3684.977
42	213.0	198.1	—	3684.885	3684.887	3684.904	3684.908	3684.925	3684.928	3684.742
60	304.5	289.6	—	—	—	3684.905	—	—	—	—
63	319.7	304.8	152.4	—	—	3684.906	3684.909	3684.926	3684.929	—
84	426.4	411.5	203.2	3684.886	3684.888	3684.907	3684.910	3684.927	3684.930	3684.743
85	431.5	431.5	203.2	—	—	3684.744	3684.745	3684.746	3684.747	3684.748

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wakefield Thermal:](#)

[3684891](#) [3684893](#) [3684895](#) [3684896](#) [3684898](#) [3684904](#) [3684907](#) [3684910](#) [3684913](#) [3684917](#) [3684922](#)
[3684927](#)